




RAST 5

TE Internal #: 2292457-3
PCB Mount Header, Vertical, Wire-to-Board, 3 Position, 5 mm [.197 in] Centerline, Fully Shrouded, Tin (Sn), Through Hole - Solder, Power, RAST 5

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**
PCB Mount Orientation: **Vertical**
Connector System: **Wire-to-Board**
Number of Positions: **3**
Number of Rows: **1**

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	3
Keying & Polarized Rib Location	1c,1d,2c,3d
PCB Mount Orientation	Vertical
Number of Positions	3
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------



Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	3.8 µm[149.6 µin]
Mating Tab Width	6.3 mm[.248 in]
PCB Contact Termination Area Plating Material Thickness	3.8 µm[149.6 µin]
Contact Shape & Form	Rectangular
Contact Layout	Inline
Contact Base Material	Copper Alloy
Mating Tab Thickness	.8 mm[.032 in]
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material	Tin (Sn)
Contact Type	Tab
Contact Current Rating (Max)	16 A

Termination Features

Square Termination Post & Tail Dimension	.8 mm[.032 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Mating Retention Type	Latch
Mating Retention	With
Mating Alignment Type	Polarization
PCB Mount Alignment Type	Locating Posts
PCB Mount Retention	Without
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	Nylon 66
------------------	----------



Centerline (Pitch)	5 mm[.197 in]
--------------------	---------------

Dimensions

Row-to-Row Spacing	5 mm[.197 in]
Connector Width	14.9 mm[.58 in]
Connector Height	12.8 mm[.503 in]
Connector Length	17.3 mm[.68 in]

Usage Conditions

Housing Temperature Rating	Standard
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]

Operation/Application

Solder Process Feature	Board Standoff
Circuit Application	Power

Industry Standards

Compatible With Agency/Standards Products	UL, VDE
Compatible With Approved Standards Products	UL E28476
Glow Wire Rating	Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Loose Piece
------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-2292457-2 2P, RAST 5 HEADER, PL, SHROUDED	 TE Part # 2324619-2 2P, RAST5 HEADER, PL, SHROUDED, OPPOSITE	 TE Part # 5-2232043-3 3P, RAST 5 Tab Header, THV	 TE Part # 1-2232043-3 3P, RAST 5 Tab Header, THV
 TE Part # 1969501-1 ASSY, TAB HDR, 7MM, 6.35 SERIES, 3 POS	 TE Part # 1969503-1 ASSY, TAB HDR, 7MM, 6.35 SERIES, 3 POS	 TE Part # 6-2232043-3 3P, RAST 5 Tab Header, THV	 TE Part # 2292457-4 4P, RAST 5 HEADER, PL, SHROUDED
 TE Part # 1-2232511-3 3P, RAST 5 TAB HEADER, THV	 TE Part # 2-2232043-3 3P, RAST 5 Tab Header, THV	 TE Part # 4-2232043-3 3P, RAST 5 Tab Header, THV	 TE Part # 1969522-1 ASSY, TAB HDR, EXT, 7MM, 6.35 SER, 3 POS
 TE Part # 1969521-1 ASSY, TAB HDR, EXT, 7MM, 6.35 SER, 3 POS	 TE Part # 2292457-2 2P, RAST 5 HEADER, PL, SHROUDED		



Also in the Series | RAST 5



Automotive Terminals(1)



Connector Contacts(1)



Connector Hardware(3)



Rectangular Power Connectors(134)




Standard Edge Connectors(8)



Wire-to-Board Connector Assemblies & Housings(19)

Customers Also Bought



TE Part #5-2299683-3
EP2.5 HDR 3P VERT W/O BOSS, TAPING, GREEN




TE Part #1969729-4
EP2.5 Shrouded HDR ASSY 4P VERT w /o boss




TE Part #1969729-5
EP2.5 Shrouded HDR ASSY 5P VERT w /o boss




TE Part #1721766-5
PCH-112D2-WG




TE Part #2-1744530-5
EP2.5 HDR ASSY 5P VERT W/O BOSS, BLUE




TE Part #6-1744530-4
EP2.5 HDR ASSY 4P VERT W/O BOSS, YELLOW




TE Part #4-1744530-5
EP2.5 HDR ASSY 5P VERT W/O BOSS, BLACK



TE Part #1744530-6
EP 2.5 Header no Boss 06P, Red



TE Part #2-1744530-4
EP2.5 HDR ASSY 4P VERT W/O BOSS, BLUE



TE Part #2-1744530-6
EP2.5 HDR ASSY 6P VERT W/O BOSS, BLUE



Documents

Product Drawings

3P, RAST 5 HEADER, PL, SHROUDED

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2292457-3_B1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2292457-3_B1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2292457-3_B1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RAST Connector System Catalog

English

Product Specifications

Product Specification

English

Agency Approvals

VDE Certificate

English