

Productname : STRIPING PAINT **Creationdate :** 17.01.20 Version : 5.0
Ref.Nr.: BDS001274_3_20200117 (EN) **Replaces:** BDS001274_20191211

Classification is based on test data.

Health: Eye irritation, category 2
 Causes serious eye irritation.
 Specific target organ toxicity - single exposure, category 3
 May cause drowsiness or dizziness.

Classification based on calculation method.

Environment: Not classified

Classification based on calculation method.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Product identifier: Contains:
 ethyl acetate
 n-butyl acetate

Hazard pictogram(s):



Signal word: Danger

Hazard statement(s): H222 : Extremely flammable aerosol.
 H229 : Pressurised container: May burst if heated.
 H319 : Causes serious eye irritation.
 H336 : May cause drowsiness or dizziness.

Precautionary statement(s): P102 : Keep out of reach of children.
 P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
 P211 : Do not spray on an open flame or other ignition source.
 P251 : Do not pierce or burn, even after use.
 P261 : Avoid breathing dust/fume/gas/mist/vapours/spray.
 P280 : Wear protective gloves/protective clothing/eye protection/face protection.
 P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.

Supplemental Hazard information: Contains:
 phthalic anhydride
 May produce an allergic reaction.

Dir. 2004/42/EC on the limitation of emissions of volatile organic compounds (VOC) of organic solvents in certain paints and varnishes and vehicle refinishing products Cat.II B (e) - VOC max. 840 g/l

2.3. Other hazards

No information available

SECTION 3: Composition/information on ingredients

3.1. Substances



Productname : STRIPING PAINT **Creationdate :** 17.01.20 Version : 5.0
Ref.Nr.: BDS001274_3_20200117 (EN) **Replaces:** BDS001274_20191211

Not applicable.

3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
dimethyl ether	01-2119472128-37	115-10-6	204-065-8	25-50	Flam. Gas 1, Press. Gas	H220,H280	A
ethyl acetate	01-2119475103-46	141-78-6	205-500-4	10-25	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	B

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes :	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Contact with skin :	Take off contaminated clothing and wash before reuse. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
Inhalation :	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
Ingestion :	If swallowed accidentally, do not induce vomiting and seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	May cause irritation. Symptoms : redness and pain
Eye contact :	Irritating to eyes Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice :	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent



Productname : STRIPING PAINT
Ref.Nr.: BDS001274_3_20200117 (EN)

Creationdate : 17.01.20 Version : 5.0
Replaces: BDS001274_20191211

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material
Place in appropriate container

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
Take precautionary measures against static discharges
Equipment should be earthed
Use explosion-proof electrical/ventilating/lighting/.../equipment.
Use only non-sparking tools.
Do not breathe aerosols or vapours.
Ensure adequate ventilation
Avoid contact with skin and eyes.
Wash thoroughly after use
Wear protective gloves/protective clothing/eye protection/face protection.
Eyewash bottles should be available



Productname : STRIPING PAINT **Creationdate :** 17.01.20 Version : 5.0
Ref.Nr.: BDS001274_3_20200117 (EN) **Replaces:** BDS001274_20191211

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
 Keep out of reach of children.

7.3. Specific end use(s)

Paints

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
dimethyl ether	115-10-6	TWA	1000 ppm
ethyl acetate	141-78-6	TWA	200 ppm
		STEL	400 ppm
National established exposure limits, United Kingdom			
dimethyl ether	115-10-6	TWA	400 ppm
		STEL	500 ppm
ethyl acetate	141-78-6	TWA	200 ppm
		STEL	400 ppm
National established exposure limits, Ireland			
dimethyl ether	115-10-6	TWA	1000 ppm
		STEL	-
ethyl acetate	141-78-6	TWA	200 ppm
		STEL	400 ppm

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation Wear suitable protective gloves
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equipped with organic gas/vapor cartridge (type A or AX) in combination with an oil proof solid and liquid particulate filter
hands and skin :	When handling the product wear chemical-resistant gloves (standard EN 374). The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.
Recommended gloves:	(polyvinylalcohol)



Productname : STRIPING PAINT **Creationdate :** 17.01.20 Version : 5.0
Ref.Nr.: BDS001274_3_20200117 (EN) **Replaces:** BDS001274_20191211

eyes : Wear safety eyewear according to EN 166.
Environmental protection: Avoid release to the environment.
Collect spillage.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Appearance : physical state : DME propelled liquid.
colour : Coloured.
odour : Characteristic odor.
pH : Not available.
Boiling point/range : 55 °C
Flash point : - 37 °C
Evaporation rate : Not available.
Explosion limits : upper limit : Not available.
lower limit : Not available.
Vapour pressure : < 110 kPa.
Relative density : 1.0 g/cm³ (@ 20°C).
Solubility in water : Not available.
Auto-ignition : Not available.
Viscosity : Not available.

9.2. Other information

VOC = volatile organic compounds 586 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials



Productname : STRIPING PAINT Creationdate : 17.01.20 Version : 5.0
 Ref.Nr.: BDS001274_3_20200117 (EN) Replaces: BDS001274_20191211

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

acute toxicity: based on available data the classification criteria are not met
skin corrosion/irritation: based on available data the classification criteria are not met
serious eye damage/irritation: Causes serious eye irritation.
respiratory or skin sensitisation: based on available data the classification criteria are not met
germ cell mutagenicity: based on available data the classification criteria are not met
carcinogenicity: based on available data the classification criteria are not met
toxicity for reproduction: based on available data the classification criteria are not met
STOT-single exposure: May cause drowsiness or dizziness.
STOT repeated exposure: based on available data the classification criteria are not met
aspiration hazard: based on available data the classification criteria are not met

Information on likely routes of exposure:

Inhalation : Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion : May cause gastrointestinal disturbances
Skin contact : May cause irritation.
Eye contact : Irritating to eyes

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
dimethyl ether	115-10-6	LC50 inhal.rat	309 mg/l
ethyl acetate	141-78-6	LD50 oral rat	5620 mg/kg
		LC50 inhal.rat	30 mg/l
		LD50 derm.rabit	> 20000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Not classified

Ecotoxicological data:



Productname : STRIPING PAINT
Ref.Nr.: BDS001274_3_20200117 (EN)

Creationdate : 17.01.20 Version : 5.0
Replaces: BDS001274_20191211

Hazardous ingredient	CAS-nr.	method	
dimethyl ether	115-10-6	IC50 algae	154.9 mg/l
		LC50 fish	4.1 mg/l
		EC50 daphnia	4.4 mg/l
ethyl acetate	141-78-6	IC50 algae	5600 mg/l
		LC50 fish	230 mg/l
		EC50 daphnia	610 mg/l

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

No experimental data available

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No experimental data available
GWP (global warming potential): 1

SECTION 13: Disposal considerations

13.1. Waste treatment methods

National regulations : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS

14.3. Transport hazard class(es)



Productname : STRIPING PAINT
Ref.Nr.: BDS001274_3_20200117 (EN)
Creationdate : 17.01.20 Version : 5.0
Replaces: BDS001274_20191211

Class: 2.1
ADR/RID - Classification code: 5F

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No
IMDG - Marine pollutant: No
IATA/ICAO - Environmentally hazardous: No

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)
IMDG - Ems: F-D, S-U
IATA/ICAO - PAX: 203
IATA/ICAO - CAO: 203

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
Regulation (EC) No 1907/2006 (REACH)
Regulation (EC) No 1272/2008 (CLP)
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation hazard statements: H220 : Extremely flammable gas.
H225 : Highly flammable liquid and vapour.
H280 : Contains gas under pressure; may explode if heated.
H319 : Causes serious eye irritation.
H336 : May cause drowsiness or dizziness.

REVISIONS IN CHAPTRE : Classification according to Regulation (EC) No 1272/2008
Labelling according to Regulation (EC) No 1272/2008



Productname :	STRIPING PAINT	Creationdate :	17.01.20 Version : 5.0
Ref.Nr.:	BDS001274_3_20200117 (EN)	Replaces:	BDS001274_20191211

8.2. Exposure controls

acronyms and synonyms:

TWA = time weight average

STEL = short time exposure limit

VOC = volatile organic compounds

PBT = persistent bioaccumulative toxic

vPvB = very persistent very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

