

Parker Product Datasheet



The main function of Ermeto DIN banjo fittings is to connect different numbers of tubes or hoses. This broad range of DIN fittings is available in steel and in stainless steel.

PART NUMBER: WHK25SRCSCF
SHAPE: Elbow 90°
CONNECTION 1 SIZE: 25 mm (O.D.)
BODY MATERIAL: Steel
CONNECTION 1 TYPE: Male 24° Cone
PRODUCT SERIES: EO Heavy
ACCESSORIES INCLUDED: Pre-assembled with Nut and EO-PSR Cutting Ring
CONNECTION 2 TYPE: Male BSPP
CONNECTION 2 SIZE: G 1 A
SEAL TYPE: Soft Seal

PRODUCT OVERVIEW

Banjo fittings are used in applications with limited space that involve high working pressure levels.

In the past, the Parker banjo fitting product range has included the W H (high-pressure resistant), SWVE (compact design) and DSVW (very good flow) properties series.

Now, we have combined these 3 series to create the new WHK series, uniting all of the advantages of our former banjo fitting designs.

Besides the product features also the product safety was improved. By the new design banjo bolts can not fall out during assembly thanks to the optimized design. Above that a mix-up between metric and inch dimensions is not possible anymore.

Markets:

- Automotive
- Defence
- Energy
- Environment
- Industrial
- Infrastructure
- Machine Tools
- Materials Handling
- Mobile
- Oil and Gas
- Power Generation
- Process
- Transportation
- Water

Applications:

Suitable for general hydraulic applications.

Features/ benefits:

- High-pressure resistant (up to 420 bar)
- Compact design
- Soft-sealing system with outstanding sealing properties
- Low pressure loss thanks to optimized banjo bolt design with angled drilling
- 2-in-1: Metal sealing version available - no additional metal sealing ring required
- Improved security
- Improved warehouse management

TECH SPECIFICATIONS

DIVISION	High Pressure Connectors Europe Division
DIVISION	High Pressure Connectors Europe Division
MAXIMUM OPERATING PRESSURE	250 bar

FOR FLUID TYPE	Gases
FOR FLUID TYPE	Hydraulic Fluids
FOR FLUID TYPE	Fuels
FOR FLUID TYPE	Steam
FOR FLUID TYPE	Chemicals
INDUSTRY	Material Handling
INDUSTRY	Agriculture
INDUSTRY	Transportation
INDUSTRY	Industrial Manufacturing Equipment
INDUSTRY	Construction
INDUSTRY	Marine
INDUSTRY	Automotive
SPECIFICATIONS MET	DIN
SPECIFICATIONS MET	ISO 8434
SHAPE	Elbow 90°
APPLICATION	Oilfield
APPLICATION	Fuel Transfer
APPLICATION	Hydraulics
APPLICATION	Chemical Transfer
APPLICATION	Mobile Equipment
APPLICATION	Packaging
BRAND	Ermeto
TECHNOLOGY	Fluid & Gas Handling
PRODUCT STYLE	Banjo
CONNECTION 1 SIZE	25 mm Tube O.D.
BODY MATERIAL	Steel
CONNECTION 1 TYPE	24° Cone

CONNECTION 1 TYPE	Male
PRODUCT SERIES	EO Heavy
PRODUCT TYPE	Hydraulic DIN Fittings
SEAL MATERIAL	NBR (Eolastic)
CONFIGURATION	Tube to Port
ACCESSORIES INCLUDED	Pre-assembled with Nut and EO-PSR Cutting Ring
CONNECTION 2 TYPE	BSPP
CONNECTION 2 TYPE	Male
CONNECTION 2 SIZE	G 1 A inch Thread
MAXIMUM AMBIENT TEMPERATURE	120 °C
MAXIMUM AMBIENT TEMPERATURE	248 °F
MINIMUM AMBIENT TEMPERATURE	-40 °C
MINIMUM AMBIENT TEMPERATURE	-40 °F
MAXIMUM FLUID TEMPERATURE	120 °C
MAXIMUM FLUID TEMPERATURE	248 °F
MINIMUM FLUID TEMPERATURE	-40 °C
MINIMUM FLUID TEMPERATURE	-40 °F
SEAL TYPE	Soft Seal