



### Main

Range of product	Odace
Product or component type	Dimmer
Device presentation	Mechanism with fixing frame
Device application	Resistive load Capacitive load Inductive load
Colour tint	Cobalt blue
Type of packing	Box with eurohole
Additional information	2-wire connection
Condition of use	Indoor

### Complementary

Device mounting	Flush
Switch function	1-pole 2-way
Fixing mode	By screws
Dimmer control	Rotary push type
Load type	230 V AC incandescent lamp: 3...100 W 230 V AC halogen lamp: 3...100 W LED lamp Low voltage halogen lamp with electronic transformer Low voltage halogen lamp with ferromagnetic transformer
[Ue] rated operational voltage	230 V AC 50/60 Hz
Protection type	Circuit breaker protection
Number of terminals	4 screw terminals
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1.5...2.5 mm <sup>2</sup> for solid cable(s) 1.5...2.5 mm <sup>2</sup> for stranded cable(s) 1.5...2.5 mm <sup>2</sup> for flexible cable(s)
Wire stripping length	8 mm
Height	71 mm
Width	71 mm
Depth	49.5 mm
Embedding depth	29.3 mm
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. This information is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...35 °C
Standards	EN 60669-2-1 2004/108/EC 2006/95/EEC
IK degree of protection	IK02
IP degree of protection	IP20

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>