


## 2 Port PCI RS422/485 Serial Adapter Card with 161050 UART

Product ID: PCI2S4851050



The PCI2S4851050 2-Port PCI Serial Adapter Card (RS422/RS485) with 161050 UART adds two DB9 RS422/RS485 serial ports, using a single PCI expansion slot.

The PCI serial card offers a high performance 16C1050 UART and supports both 2-wire and 4-wire RS485 modes. The card delivers an efficient single-chip design and a large 256-byte transmit/receive FIFO buffer that work together to provide high-speed serial communication while reducing the overall load on the system CPU.

With the included standard and low profile/half-height brackets, this PCI serial expansion card suits a broad range of system form factors, and is a perfect addition for connecting RS422/485 serial devices to a host computer. For added versatility, the RS422/RS485 adapter is able to accommodate 3.3 or 5V PCI/PCI-X slots.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Add RS422 and RS485 (2 or 4-wire) support to a Desktop, Server or Embedded system
- For use in industrial environments with serial networking devices, high speed modems, monitoring equipment, long distance communication devices and printers
- Ideal for commercial and industrial applications such as POS networks, ATMs, bank teller stations, and CNC based production lines
- Works for industrial process control and factory automation applications

### Features

- Supports maximum data transmission rate of 128Kbps
- 16C1050 UART with 256-byte Deep FIFO
- Supports 2-wire and 4-wire RS485 modes
- Jumper pins for RS422/485 toggling
- Supports Hardware and Software flow control
- Supports PCI Power Management 1.1
- Compliant with PCI Local Bus Specification 2.3

<b>Hardware</b>	Warranty	Lifetime
	Bus Type	PCI / PCI-X (5 / 3.3V)
	Card Type	Standard Profile (LP bracket incl.)
	Chipset ID	SystemBase - SB16C1052PCI
	Industry Standards	PCI Local Bus Specification 2.3 PCI Power Management 1.1
	Interface	Serial
	Port Style	Integrated on Card
	Ports	2
<b>Performance</b>	Data Bits	5, 6, 7, 8
	FIFO	256 Bytes
	Flow Control	Xon, Xoff
	Max Baud Rate	128 Kbps
	Parity	Even, Odd, or No Parity
	Serial Protocol	RS-422/485
	Stop Bits	1, 1.5, 2
<b>Connector(s)</b>	Connector Type(s)	1 - PCI / PCI-X (Universal 3.3 & 5V, 32-bit) Male
	External Ports	2 - DB-9 (9 pin, D-Sub) Male
<b>Software</b>	OS Compatibility	Windows® XP, Vista, 7, 8, 8.1, 10 Windows Server® 2000, 2003, 2008 R2, 2012, 2016
<b>Environmental</b>	Humidity	5~85% RH
	Operating Temperature	-10°C to 80°C (14°F to 176°F)
	Storage Temperature	-20°C to 100°C (-4°F to 212°F)
<b>Physical Characteristics</b>	Product Height	1.8 in [4.5 cm]
	Product Length	4.7 in [12 cm]
	Product Width	0.6 in [15 mm]
	Weight of Product	2 oz [58 g]
<b>Packaging Information</b>	Package Height	1.3 in [32 mm]
	Package Length	6.9 in [17.5 cm]
	Package Width	5.7 in [14.5 cm]
	Shipping (Package) Weight	0.3 lb [0.2 kg]

---

<b>What's in the Box</b>	Included in Package
	1 - 2 port PCI RS422/485 card
	2 - Low profile (half-height) brackets
	1 - Driver CD
	1 - User Manual

---

Product appearance and specifications are subject to change without notice.