




Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **TPA (Terminal Position Assurance)**

Number of Positions: **10**

Operating Temperature (Max): **105 °C [221 °F]**

Operating Temperature Range: **-40 – 105 °C [-40 – 221 °F]**

Hardware Accessory Function: **Position Assurance**

Features

Product Type Features

Connector Hardware Accessory Type	TPA (Terminal Position Assurance)
Hardware Accessory Function	Position Assurance

Configuration Features

Number of Positions	10
---------------------	----

Dimensions

Product Width	5.4 mm[.213 in]
Product Length	47 mm[1.85 in]
Product Height	4.35 mm[.171 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features



Packaging Method	Bag/Box
Packaging Quantity	6000

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1969608-2
12P VAL-U-LOK TPA 22-18 AWG



TE Part # 1969608-9
9P VAL-U-LOK TPA 22-18 AWG



TE Part # 1-1969609-0
10P VAL-U-LOK TPA 26-22 AWG



TE Part # 1969608-3
3P VAL-U-LOK TPA 22-18 AWG





TE Part # 1969608-5
5P VAL-U-LOK TPA 22-18 AWG



TE Part # 1969608-2
2P VAL-U-LOK TPA 22-18 AWG



TE Part # 1969608-8
8P VAL-U-LOK TPA 22-18 AWG



TE Part # 1969608-6
6P VAL-U-LOK TPA 22-18 AWG



TE Part # 1969608-7
7P VAL-U-LOK TPA 22-18 AWG



TE Part # 1-1969608-1
11P VAL-U-LOK TPA 22-18 AWG



TE Part # 1969608-1
1P VAL-U-LOK TPA 22-18 AWG



TE Part # 1969608-4
4P VAL-U-LOK TPA 22-18 AWG

Customers Also Bought




TE Part #638652-1
RECEPT,1.5MM,TIN 14-16AWG RD=1



TE Part #HDP26-18-20PN
PLG, 20P, BLK, N, 16/20, P



TE Part #2238020-1
VAL-U-LOK PIN BR TN 22-18 LP




TE Part #2302454-3
1-PORT MATENET FRAME,UTP, COD C




TE Part #1969608-1
1P VAL-U-LOK TPA 22-18 AWG



TE Part #2302452-3
MATENET, FIXATION ELEMENT




TE Part #925475-1
FF 110 REC HSG 3P NYLON NAT



TE Part #1586861-6
6P PM PLUG VAL-U-LOK PM GW



TE Part #925015-1
FF 110 REC HSG 3P NYLON BLACK



TE Part #174931-1
070 MLC W-W CAP HSG 8P NATURAL

Documents



Product Drawings

10P VAL-U-LOK TPA 22-18 AWG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1969608-0_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1969608-0_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1969608-0_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773730-3 VAL-U-LOK Connectors with TPA Flyer

English

Product Specifications

Application Specification

English