

## Analogue 7 Day Panel 16921 & 16922 (without battery reserve)



### Benefits

---

A very simple to use and cost effective general purpose 7 day timer, that is ideal for many applications. Each tappet around the analogue clock represents 1 hour. An optional panel mount kit is available for when the back box provided is not suitable. The 16921 includes a 200 hour battery reserve, while the 16922 has no battery reserve.

### Features


---

- Programming in steps of one hour
- Minimum interval between 2 switchings: 2 hours (two tappets)
- 84 switchings per week
- Switching accuracy: 10 minutes
- Programming by captive segments. A red zone is uncovered when a tappet is moved to the ON status and is hidden when the tappet is moved to the OFF position.
- Time of day shown by hands, allowing time setting
- by simple rotation in either direction. Summer/Winter time corrections are made easily.
- Manual override with automatic return to program. Contact status display
- Terminals in housing which opens for easy wiring.
- Surface, Panel or Din rail mounting
- Voltage free 16A changeover contact
- Panel Mounting Options
- Fit using supplied back box - maximum panel thickness - 2mm (Connections made into back box)
- Fit using BR6 panel mounting kit - maximum panel thickness - 4mm (Connections made via tab terminals - back box discarded)

## Technical Data

Supply voltage	230V + 10% -15%
Frequency	50/60 Hz
Power consumption	approx. 0.5 VA
Voltage free changeover contacts	16 (3) A
Changeover contacts	
resistive load	16 A 250 V
voltage free inductive load (cos = 0.6)	3 A 250 V
incandescent lamps	1000 W 250 V
squirrel-cage motor	350 W 250 V
Time base	Quartz
Accuracy of operation	1 sec / 24 h.
Operating temperature	-10°C to +50°C
Storage temperature	-20°C to +60°C
Connection by cage terminals, section of conductors	1 to 6 mm <sup>2</sup>
Insulation class	II
Protection index IP 20	
Conformity to standard BS EN 60730	yes
Performance indicated for an ambient temperature of 20°C	

## Electrical Connections



## Technical Helpline: 01475 745131

### CUSTOMER CARE POLICY

As part of Sangamo's continuous improvement program, the Company operates a Customer Care Policy. This means that we welcome your comments and complaints, as it can only help us to improve our services to you, our customer.

**SANGAMO**



Certificate Q05237



Certificate EMS 80426

Sangamo Limited, Industrial Estate, Port Glasgow,  
Renfrewshire PA14 5XG

Tel: 01475 745131 Fax: 01475 744567

Email : enquiries@sangamo.co.uk Web: www.sangamo.co.uk