


# WORKSHOP SERVICE TROLLEY (2 & 3 SHELF)

## Assembly Instructions

1. TO BOLT LOWER TRAY > ALIGN HOLES ON 4 x POSTS(G) AT MATCHING HOLES ON TRAY CORNERS
2. ONLY APPLIES TO 3 SHELF TROLLEY VERSION > REPEAT POINT 1 TO BOLT MIDDLE TRAY(E) TO CENTER HOLES ON POST
3. TO BOLT UPPER TRAY TO POST > USE STANDARD BOLTS FOR THE TRAY SIDE WITHOUT THE HANDLE ATTACHMENT + TO BOLT HANDLE & BRACKETS (D + H) TO POST AT POSITION (A) USE THE 4 LONGER BOLTS
4. TO ATTACH EACH CASTOR(C + F) THROUGH HOLES ON THE UNDERSIDE OF LOWER TRAY(B), ALIGN THE CASTOR BRACKET HOLES TO MATCHING HOLES ON UNDERSIDE OF TRAY

**NOTE: USE BOLTS, ROUND WASHERS ON OUTSIDE OF POSTS & USE BLACK WASHERS AND NUTS ON THE INSIDE OF TRAYS .**



PRODUCT SPECIFICATION/S
Size:(mm): L1020xW620xH820
Capacity(kg): 250
Wheel type: Rubber Cushion
Wheel size: 125mm

	COMPONENT	QTY	NOTES
A	UPPER TRAY	1	
B	LOWER TRAY	1	USE GRIP PLIERS & 1/2" SOCKET/RACHET FOR WHEEL BOLTS
C	SWIVEL CASTOR	2	
D	HANDLE	1	
E	MIDDLE TRAY	1	MIDDLE TRAY ONLY APPLIES TO 3 SHELF TROLLEY VERSION
F	FIXED CASTOR	2	
G	POST	4	
H	HANDLE BRACKET	2	USE 4 LONGER BOLTS



2 SHELF TROLLEY



3 SHELF TROLLEY