

Product type designation

SFP991-1

SCALANCE X accessory; Plug-in transceiver SFP991-1; 1x 100 Mbit/s LC port, optical; multimode optical up to max. 5 km



Interfaces

Number of electrical/optical connections / for network components or terminal equipment / maximum	1
Number of optical interfaces / for network components or terminal equipment / maximum	1
Number of 100 Mbit/s LC ports	1
Design of the optical interface / for network components or terminal equipment	LC
Wavelength / of the optical interface	1310 nm; Multi-mode
Connectable optical power relative to 1 mW	
<ul style="list-style-type: none"> • of the transmitter output / minimum • of the transmitter output / maximum • of the receiver input / maximum 	<p>-24 dB</p> <p>-14 dB</p> <p>-12 dB</p>
Optical sensitivity relating to 1 mW / of the receiver input / minimum	-31 dB
Damping ratio / of the FOC transmission link / minimum necessary	0 dB
Range / at the optical interface / depending on the optical fiber used	0 ... 5 km

Ambient conditions

Ambient temperature	
• during operation	-40 ... +85 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
• Note	A maximum operating temperature of +85 °C is permissible for a duration of 16 hours
Relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
Protection class IP	IP20

Design, dimensions and weights

Design	SFP Module
Width	14 mm
Height	9 mm
Depth	57 mm
Net weight	0.01 kg
Mounting type	latched

Standards, specifications, approvals

Standard	
• for FM	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4
• for hazardous zone	EN 60079-0: 2006, EN60079-15: 2005, II 3 G Ex nA II T4, KEMA 07 ATEX 0145 X
• for safety / from CSA and UL	UL 60950-1, CSA C22.2 No. 60950-1-03
• for emitted interference	EN 61000-6-4:2007 (Class A)
• for interference immunity	EN 61000-6-2:2005
Certificate of suitability	EN 61000-6-2:2005, EN 61000-6-4:2007
• CE marking	Yes
• C-Tick	Yes
• KC approval	No
Marine classification association	
• Bureau Veritas (BV)	Yes
MTBF	490 y

Further information / Internet-Links

Internet-Link	
• to website: Selector SIMATIC NET SELECTION TOOL	http://www.siemens.com/snst
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx Download Manager	http://www.siemens.com/cax

- to website: Industry Online Support

<https://support.industry.siemens.com>

last modified:

05/08/2020