


Geberit Mapress ball valve, NPW, with spindle extension



Example image



APPLICATION PURPOSES

- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For compressed air (oil purity class 0–3)
- For installations with Geberit Mapress Carbon Steel
- For installations with Geberit Mapress Copper

CHARACTERISTICS

- Ball made of brass, chrome-plated
- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

TECHNICAL DATA

Operating temperature	-20 – +120 °C
Product material	Brass CW617N

INFO

- The ball valves are marked with PN 10 on the body in accordance with DVGW and EN 13828
- The ball valves are approved for up to PN 16

Art. no.	DN	DNV	d, ø mm	L cm	L1 cm	L2 cm	Z cm	Z1 cm	PN bar
94962	12	15	15	7.7	10.4	8.5	1.7	2.4	16
94963	15	15	18	8	10.4	8.5	1.7	2.4	16
94964	20	20	22	8.9	11.7	10.6	2.1	2.9	16
94965	25	25	28	9.6	12.1	10.6	2.4	3.1	16

<i>Art. no.</i>	<i>DN</i>	<i>DNV</i>	<i>d_ø</i> <i>mm</i>	<i>L</i> <i>cm</i>	<i>L1</i> <i>cm</i>	<i>L2</i> <i>cm</i>	<i>Z</i> <i>cm</i>	<i>Z1</i> <i>cm</i>	<i>PN</i> <i>bar</i>
94966	32	32	35	10.9	12.6	10.6	2.7	3.4	16
94967	40	40	42	14.1	14	15	3.6	4.5	16
94968	50	50	54	15.7	15.5	17	3.9	4.8	16