

Features

- Type K Temperature Handle Probe.
- 2m Fully Extended Retractable Curly Thermocouple Lead - Polyurethane outer.
- IEC colour coded.
- The International Electrotechnical Commission (IEC) is an international standards organisation that prepares and publishes international standards.

RS PRO Thermocouple Right Angled Surface Probe - Type K IEC

RS Stock No.: 174-1675



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Type K Temperature Handle Probe with 2 metres retractable curly lead, terminating in a miniature plug.

General Specifications

General Description	Stainless steel sheath with a moulded handle and 2 metres of coiled extension cable terminated in a miniature thermocouple plug.
---------------------	--

Mechanical Specifications

Colour Code	K IEC
Sensor Type	Right Angled Surface Probe Type K IEC
Thermocouple Type	K
Probe Tip Type	Ceramic Tip, Coiled Element
Probe Diameter	12mm Tip
Probe Length	180mm
Cable Length	2m Fully Extended
Cable Type	Retractable Curly Thermocouple Lead - Polyurethane outer
Termination	Miniature Plug
Maximum Temperature Measurement	900°C
Dimensions	Probe Ø12mm Tip x 40mm Hot Leg and Ø6mm x 180mm Cold Leg. Coiled element diameter 7mm

Approvals

RoHS Compliant	Yes
Standards Met	IEC