

**Safety data sheet
according to UK REACH**

Printing date 30.01.2026

Version number 5 (replaces version 4)

Revision: 28.08.2023

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1 Product identifier****Trade name:** SurfacePro Glass Cleaner CA 40 R eco!perform**1.2 Relevant identified uses of the substance or mixture and uses advised against**

No further relevant information available.

Application of the substance / the mixture Glass Cleaner**1.3 Details of the supplier of the safety data sheet****Manufacturer/Supplier:****Alfred Kärcher SE & Co. KG**

Alfred-Kärcher-Str. 28-40

D - 71364 Winnenden

Tel.: +49-7195-14-0

Kärcher (UK) Ltd.

Kärcher House

Brookhill Way

Banbury

Oxon OX16 3ED

Great Britain

Tel.: +44-1295-752-000

Internet: www.karcher.com**Further information obtainable from:**

Regulatory Affairs

Tel.: +49-7195-14-0

productsafety.management.de@karcher.com**1.4 Emergency telephone number:**

For Hazardous Materials [or Dangerous Goods] Incidents

Spill, Leak, Fire, Exposure, or Accident

Call CHEMTREC Day or Night

Within USA and Canada: 1-800-424-9300

Outside USA and Canada: +1-703-527-3887 (collect calls accepted)

SECTION 2: Hazards identification**2.1 Classification of the substance or mixture****Classification according to Regulation (EC) No 1272/2008**

The product is not classified, according to the GB CLP regulation.

2.2 Label elements**Labelling according to Regulation (EC) No 1272/2008** Void**Hazard pictograms** Void**Signal word** Void**Hazard statements** Void

(Contd. on page 2)

GB

Safety data sheet
according to UK REACH

Printing date 30.01.2026

Version number 5 (replaces version 4)

Revision: 28.08.2023

Trade name: SurfacePro Glass Cleaner CA 40 R eco!perform

(Contd. of page 1)

- **Additional information:**
Safety data sheet available on request.

SECTION 3: Composition/information on ingredients

- **3.2 Mixtures**
- **Description:** Cleaning agent

· **Dangerous components:**

CAS: 67-63-0 EINECS: 200-661-7 Index number: 603-117-00-0 Reg.nr.: 01-2119457558-25-xxxx	propan-2-ol ⚠ Flam. Liq. 2, H225; ⚠ Eye Irrit. 2, H319; STOT SE 3, H336	≥5-<10%
CAS: 57-55-6 EINECS: 200-338-0 Reg.nr.: 01-2119456809-23-xxxx	Propylene glycol substance with a Community workplace exposure limit	1-5%

- **Additional information** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **After inhalation** Supply fresh air; consult doctor in case of complaints.
- **After skin contact** Generally the product does not irritate the skin.
- **After eye contact** Rinse opened eye for several minutes under running water.
- **After swallowing**
Rinse out mouth and then drink plenty of water.
If symptoms persist consult doctor.
- **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents**
CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **5.2 Special hazards arising from the substance or mixture** No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:** No special measures required.

(Contd. on page 3)

Safety data sheet according to UK REACH

Printing date 30.01.2026

Version number 5 (replaces version 4)

Revision: 28.08.2023

Trade name: SurfacePro Glass Cleaner CA 40 R eco!perform

(Contd. of page 2)

- **Additional information** Collect contaminated fire fighting water separately. It must not enter the sewage system.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures** Not required
- **6.2 Environmental precautions:**
Dilute with plenty of water.
Do not allow to enter sewers/ surface or ground water.
Do not allow to penetrate the ground/soil.
- **6.3 Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders).
- **6.4 Reference to other sections**
See Section 7 for information on safe handling
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** No special precautions are necessary if used correctly.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Keep away from food, beverages and feed.
- **Further information about storage conditions:** None.
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **8.1 Control parameters**

- **Ingredients with limit values that require monitoring at the workplace:**

67-63-0 propan-2-ol

WEL	Short-term value: 1250 mg/m ³ , 500 ppm
	Long-term value: 999 mg/m ³ , 400 ppm

57-55-6 Propylene glycol

WEL	Long-term value: 474* 10** mg/m ³ , 150* ppm
	*total vapour and particulates **particulates

(Contd. on page 4)

Safety data sheet according to UK REACH

Printing date 30.01.2026

Version number 5 (replaces version 4)

Revision: 28.08.2023

Trade name: SurfacePro Glass Cleaner CA 40 R eco!perform

(Contd. of page 3)

· DNELs

67-63-0 propan-2-ol

Oral	DNEL	26 mg/kg×d (consumer)
Dermal	DNEL	888 mg/kg×d (employee)
		319 mg/kg×d (consumer)
Inhalative	DNEL	500 mg/m3 (employee)
		89 mg/m3 (consumer)

57-55-6 Propylene glycol

Oral	DNEL	85 mg/kg×d (consumer)
Dermal	DNEL	213 mg/kg×d (consumer)
Inhalative	DNEL	168 mg/m3 (employee)
		50 mg/m3 (consumer)

· PNECs

67-63-0 propan-2-ol

PNEC	140.9 mg/l (freshwater)
	140.9 mg/l (marine water)
	140.9 mg/l (STP)
	2251 mg/l (STP)
PNEC sediment	552 mg/kg (freshwater)
	552 mg/kg (marine water)
PNEC soil	28 mg/kg (soil)

57-55-6 Propylene glycol

PNEC	26 mg/l (marine water)
	2000 mg/l (STP)

· 8.2 Exposure controls

- **Appropriate engineering controls** No further data; see section 7.
- **Individual protection measures, such as personal protective equipment**
- **General protective and hygienic measures** Wash hands before breaks and at the end of work.
- **Respiratory protection:** Not necessary if room is well-ventilated.
- **Hand protection** Not required
- **Material of gloves** Not required
- **Penetration time of glove material** Not required
- **Eye/face protection** Not required

SECTION 9: Physical and chemical properties

· 9.1 Information on basic physical and chemical properties

· General Information

· Physical state	Liquid
· Colour:	Colourless
· Odour:	green tea

(Contd. on page 5)

GB

Safety data sheet according to UK REACH

Printing date 30.01.2026

Version number 5 (replaces version 4)

Revision: 28.08.2023

Trade name: SurfacePro Glass Cleaner CA 40 R eco!perform

(Contd. of page 4)

· Odour threshold:	Not determined
· Melting point/freezing point:	-5 °C
· Boiling point or initial boiling point and boiling range	100 °C
· Flammability	Not applicable
· Lower and upper explosion limit	
· Lower:	Not determined
· Upper:	Not determined
· Flash point:	46 °C (Closed Cup) Does not support combustion (No. 32.5.2 UN MTC, Method L.2).
· Auto-ignition temperature:	not applicable
· Decomposition temperature:	Not determined
· pH at 20 °C	6-8
· Viscosity:	
· Kinematic viscosity	Not determined
· dynamic:	Not determined
· Solubility	
· Water:	Fully miscible
· Partition coefficient n-octanol/water (log value)	Not determined
· Vapour pressure:	Not determined
· Density and/or relative density	
· Density at 20 °C:	0.989 g/cm ³
· Relative density	Not determined
· Vapour density	Not determined
· Relative gas density	Not determined
· Particle characteristics	Not applicable

· 9.2 Other information

· Appearance:	
· Form:	Fluid
· Important information on protection of health and environment, and on safety.	
· Ignition temperature:	Product is not selfigniting.
· Explosive properties:	Product does not present an explosion hazard.
· Change in condition	
· Evaporation rate	Not determined

· Information with regard to physical hazard classes

· Explosives	Void
· Flammable gases	Void
· Aerosols	Void
· Oxidising gases	Void
· Gases under pressure	Void
· Flammable liquids	Void
· Flammable solids	Void
· Self-reactive substances and mixtures	Void
· Pyrophoric liquids	Void
· Pyrophoric solids	Void

(Contd. on page 6)

Safety data sheet according to UK REACH

Printing date 30.01.2026

Version number 5 (replaces version 4)

Revision: 28.08.2023

Trade name: SurfacePro Glass Cleaner CA 40 R eco!perform

(Contd. of page 5)

- | | |
|---|------|
| · Self-heating substances and mixtures | Void |
| · Substances and mixtures, which emit flammable gases in contact with water | Void |
| · Oxidising liquids | Void |
| · Oxidising solids | Void |
| · Organic peroxides | Void |
| · Corrosive to metals | Void |
| · Desensitised explosives | Void |

SECTION 10: Stability and reactivity

- **10.1 Reactivity** corresponds to 10.3
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known

SECTION 11: Toxicological information

- **11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**
- **Acute toxicity** Based on available data, the classification criteria are not met.

- **LD/LC50 values relevant for classification:**

67-63-0 propan-2-ol

Oral	LD50	5840 mg/kg (Rat) (OECD 401)
Dermal	LD50	13900 mg/kg (Rabbit) (OECD 402)

57-55-6 Propylene glycol

Oral	LD50	22000 mg/kg (Rat)
------	------	-------------------

- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

(Contd. on page 7)

Safety data sheet according to UK REACH

Printing date 30.01.2026

Version number 5 (replaces version 4)

Revision: 28.08.2023

Trade name: SurfacePro Glass Cleaner CA 40 R eco!perform

(Contd. of page 6)

11.2 Information on other hazards

Endocrine disrupting properties

None of the ingredients is listed.

SECTION 12: Ecological information

12.1 Toxicity

Aquatic toxicity:

67-63-0 propan-2-ol

LC50/96 h	9640 mg/l (Pimephales promelas)
EC50/48 h	13299 mg/l (Daphnia magna)
EC50/72 h	>1000 mg/l (Desmodesmus subspicatus)
EC10/18 h	>1000 mg/l (Pseudomonas putida) (DIN 38412)

57-55-6 Propylene glycol

LC50/96 h	40613 mg/l (Oncorhynchus mykiss)
-----------	----------------------------------

12.2 Persistence and degradability No further relevant information available.

12.3 Bioaccumulative potential No further relevant information available.

12.4 Mobility in soil No further relevant information available.

12.5 Results of PBT and vPvB assessment

PBT: Not applicable

vPvB: Not applicable

12.6 Endocrine disrupting properties The product does not contain substances with endocrine disrupting properties.

12.7 Other adverse effects

Additional ecological information:

COD-value: 180.000 mg/l

General notes:

The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

The product does not contain organic complexing agents.

The product does not contain organically bounded halogens (AOX-free).

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

GB

(Contd. on page 8)

Safety data sheet according to UK REACH

Printing date 30.01.2026

Version number 5 (replaces version 4)

Revision: 28.08.2023

Trade name: SurfacePro Glass Cleaner CA 40 R eco!perform

(Contd. of page 7)

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Recommendation

Must not be disposed together with household garbage. Do not allow product to reach sewage system.
Must be specially treated adhering to official regulations.

European waste catalogue

20 01 30	detergents other than those mentioned in 20 01 29
----------	---

Uncleaned packaging:

Recommendation:

Empty contaminated packagings thoroughly. They may be recycled after thorough and proper cleaning.

Recommended cleansing agents: Water, if necessary together with cleaning agents.

SECTION 14: Transport information

14.1 UN number or ID number

ADR, IMDG, IATA

Void

14.2 UN proper shipping name

ADR, IMDG, IATA

Void

14.3 Transport hazard class(es)

ADR, ADN, IMDG, IATA

Class

Void

14.4 Packing group

ADR, IMDG, IATA

Void

14.5 Environmental hazards:

Not applicable

14.6 Special precautions for user

Not applicable

14.7 Maritime transport in bulk according to IMO instruments

Not applicable

UN "Model Regulation":

Void

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Directive 2012/18/EU

Named dangerous substances - ANNEX I None of the ingredients is listed.

(Contd. on page 9)

**Safety data sheet
according to UK REACH**

Printing date 30.01.2026

Version number 5 (replaces version 4)

Revision: 28.08.2023

Trade name: SurfacePro Glass Cleaner CA 40 R eco!perform*(Contd. of page 8)*

- **National regulations**
- **Information about limitation of use:** Employment restrictions concerning juveniles must be observed.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

A product information sheet can be provided if requested.

· Relevant phrases

H225 Highly flammable liquid and vapour.

H319 Causes serious eye irritation.

H336 May cause drowsiness or dizziness.

· Contact:

Regulatory Affairs

Tel.: +49-7195-14-0

productsafety.management.de@karcher.com

· Abbreviations and acronyms:

ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

DNEL: Derived No-Effect Level (UK REACH)

PNEC: Predicted No-Effect Concentration (UK REACH)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

Flam. Liq. 2: Flammable liquids – Category 2

Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

· * Data compared to the previous version altered.

· 0-011-321-0 CA 40 R/3 2-699