

Product datasheet

Specifications



servo motor MH3 100 3,3Nm,no key,single 16 lines,brake,IP65/IP67,4kRPM

MH31001P06F2200

Discontinued on: 9 Feb 2023

Discontinued

EAN Code: 3606485395845

Main

Range compatibility	PacDrive 3
Device short name	MH3
Product or component type	Servo motor

Complementary

Maximum mechanical speed	6000 rpm
[Us] rated supply voltage	115...480 V
Network number of phases	Three phase
Continuous stall current	3.15 A
Continuous stall torque	3.4 N.m, 115...480 V, three phase
Continuous power	1520 W
Peak stall torque	10.8 N.m, 115...480 V, three phase
Nominal output power	0.35 W, 115 V 0.67 W, 230 V 1.26 W, 400 V 1.52 W, 480 V
Nominal torque	3.3 N.m for LXM52 at 3.07 mA, 115 V, three phase 3.2 N.m for LXM52 at 2.99 mA, 230 V, single phase 3 N.m for LXM52 at 2.83 mA, 400 V, three phase 2.9 N.m for LXM52 at 2.75 mA, 480 V, three phase 3.3 N.m for LXM62 at 3.07 mA, 115 V, single phase 3.2 N.m for LXM62 at 2.99 mA, 230 V, single phase 3 N.m for LXM62 at 2.83 mA, 400 V, three phase 2.9 N.m for LXM62 at 2.75 mA, 480 V, three phase
Nominal speed	1000 rpm for LXM52 at 3.07 mA, 115 V, single phase 2000 rpm for LXM52 at 2.99 mA, 230 V, single phase 4000 rpm for LXM52 at 2.83 mA, 400 V, three phase 5000 rpm for LXM52 at 2.75 mA, 480 V, three phase 1000 rpm for LXM62 at 3.07 mA, 115 V, single phase 2000 rpm for LXM62 at 2.99 mA, 230 V, single phase 4000 rpm for LXM62 at 2.83 mA, 400 V, three phase 5000 rpm for LXM62 at 2.75 mA, 480 V, three phase
Maximum current Irms	11.2 A
Shaft end	Smooth shaft
Second shaft	Without second shaft end
Shaft diameter	19 mm
Shaft length	40 mm
IP degree of protection	IP65 standard

Encoder type	Single turn SinCos Hiperface
Speed feedback resolution	16 periods
Holding brake	With
Holding torque	5.5 N.m
Mounting support	International standard flange
Motor flange size	100 mm
Electrical connection	Rotatable right-angled connectors
Torque constant	1.08 N.m/A at 120 °C
Back emf constant	70.3 V/krpm
Number of motor poles	5.0
Rotor inertia	3.68 kg.cm ²
Stator resistance	4.12 Ohm
Stator inductance	14.9 mH
Stator electrical time constant	4.5 ms
Maximum radial force Fr	900 N at 1000 rpm 720 N at 2000 rpm 630 N at 3000 rpm 570 N at 4000 rpm 530 N at 5000 rpm
Brake pull-in power	12 W
type of cooling	Natural convection
Length	170.3 mm
Centring collar diameter	95 mm
centring collar depth	3.5 mm
Number of mounting holes	4
Mounting holes diameter	9 mm
Circle diameter of the mounting holes	115 mm
Net weight	4.8 kg
Sizing reference	MH31001P
Temperature copper hot	135 °C
compatible drive output current 3s peak 2	15 A

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21.0 cm
Package 1 Width	18.0 cm
Package 1 Length	35.6 cm
Package 1 Weight	4.04 kg

Contractual warranty

Warranty	18 months
----------	-----------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1437
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration
PVC free	Yes

Use Again

Repack and remanufacture

Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins