

## Features

- **Centralized Storage** – Organizes and holds LOTO procedures and binder in a single, accessible location.
- **Highly Visible Design** – Features red-and-white diagonal stripes and “LOCKOUT SAFETY PROCEDURES” signage for maximum attention.
- **Durable Build** – Constructed with an ACP (Aluminium Composite Panel) backboard and white powder-coated metal wire rack for long-lasting use.
- **Easy Installation** – Installs easily with four mounting screws (included).
- **OSHA Compliance Support** – Helps meet regulatory standards by making lockout procedures available at the point of need.
- **Ideal for Industrial Settings** – Perfect for factories, warehouses, and maintenance zones to enhance safety communication.

## RS PRO Lockout Procedure Station - Binder Holder

RS Stock No.: 0694383



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

- *The Lockout Procedure Station – Binder Holder provides a designated area for storing and displaying Lockout Tagout safety procedures.*
- *Designed to enhance visibility and accessibility of critical documentation during maintenance and servicing operations.*
- *Features a durable ACP back panel with rounded corners for a polished and safe finish.*
- *White powder-coated metal wire rack adds corrosion resistance and visibility in industrial settings.*
- *Includes one 3 ring binder holder to hold multiple LOTO procedures.*
- *Helps improve awareness of company LOTO protocols while supporting compliance with OSHA and workplace safety standards.*
- *Ideal for placement near machines, energy sources, or LOTO stations, ensuring life-saving procedures are never out of reach.*

## General Specifications

<b>Type</b>	Binder Station + 3 Ring Binder Holder
<b>Material</b>	ACP Back Panel with Metal Wires
<b>Colour</b>	White & Red
<b>Package</b>	PE-LD

## Mechanical Specifications

<b>Dimensions (Station)</b>	508mm X 356mm X 114mm
<b>Height</b>	508mm
<b>Width</b>	356mm
<b>Depth</b>	114mm
<b>Dimensions (Binder)</b>	317mm X 254mm X 63.5mm
<b>Height</b>	317mm
<b>Width</b>	254mm
<b>Depth</b>	63.5mm
<b>Weight</b>	1.9 Kgs

## Operation Environment Specifications

<b>Withstand temperature</b>	-40°C to 80°C
------------------------------	---------------