





FAG

6216-Z

Deep groove ball bearing

Deep groove ball bearing 62...-Z, single row, shield , steel sheet metal cage

Technical information



Your current product variant

Sealing	Z	Non-contact shield on one Side
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S0	Rings dimensional stabilized up to 150°
Lubricant	Without	Bearing not greased
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	80 mm	Bore diameter
D	140 mm	Outside diameter
B	26 mm	Width
C _r	77,000 N	Basic dynamic load rating, radial
C _{0r}	55,000 N	Basic static load rating, radial
C _{ur}	3,650 N	Fatigue load limit, radial
n _G	7,300 1/min	Limiting speed
n _{gr}	5,500 1/min	Reference speed
≈m	1.47 kg	Weight



Mounting dimensions

$d_{a\ min}$	91 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	129 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	2 mm	Maximum fillet radius

Dimensions

$r_{\min}$	2 mm	Minimum chamfer dimension
D_1	121.48 mm	Shoulder diameter outer ring
D_2	124.38 mm	Caliber diameter outer ring
d_1	98.5 mm	Shoulder diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	150 °C	Operating temperature max.

Calculation factors

f_0	15	Calculation factor
-------	----	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Sealed on one side