

PACT RCP-D190-10M - Coil



2910324

<https://www.phoenixcontact.com/in/products/2910324>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

600 mm long Rogowski coil. The measuring coil diameter when installed is 190 mm. The Rogowski coil is used for AC current measurement for busbars and power lines.



Commercial data

Item number	2910324
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CK4
Product key	CMMA12
Catalog page	Page 219 (C-5-2019)
GTIN	4055626437569
Weight per piece (including packing)	401.66 g
Weight per piece (excluding packing)	382 g
Customs tariff number	90309000
Country of origin	IT

PACT RCP-D190-10M - Coil

2910324

<https://www.phoenixcontact.com/in/products/2910324>



Technical data

Product properties

Product type	Rogowski coil
Set comprises	2910327 PACT RCP-4000A-1A-D190-10M

Insulation characteristics

Pollution degree	2
------------------	---

Electrical properties

Measuring coil

Conductor structure signal line	2x 0.22 mm (Signal (tinned))
	1x 0.22 mm (Shielding (tinned))
Insulation	double insulation
Rated insulation voltage	1000 V AC (rms CAT III)
	600 V AC (rms CAT IV)
Test voltage	10.45 kV DC (60 s)
Accuracy class	0.2 (IEC 61869-10: A1)

General

Converter type	Rogowski coil
----------------	---------------

Input data

Frequency

Designation	Measuring coil
Frequency measuring range	40 Hz ... 20000 Hz

Current transformer

Converter type	Rogowski coil
----------------	---------------

Output data

Signal

Designation	Measuring coil
Output signal (at 50 Hz)	100 mV (no load, at 1,000 A)
Output voltage (in no-load operation)	$V_{OUT} = M \cdot dI/dt$
Output voltage (sinusoidal, in no-load operation)	100 mV ($V_{OUT} = 2 \cdot \pi \cdot M \cdot f \cdot I$ ($M = 0.318 \mu H$; example: At 50 Hz; $I = 1,000 A$))

Dimensions

Measuring coil

Length	600 mm
Diameter	8.3 mm ± 0.2 mm

Measuring coil when installed

PACT RCP-D190-10M - Coil



2910324

<https://www.phoenixcontact.com/in/products/2910324>

Diameter	190 mm
----------	--------

Signal line

Length	10 m
--------	------

Material specifications

Housing material	PC
Coil material	Elastollan

Environmental and real-life conditions

Ambient conditions

Measuring coil degree of protection	IP54 (not assessed by UL)
Ambient temperature (operation)	-30 °C ... 80 °C (Measuring coil)
Ambient temperature (storage/transport)	-40 °C ... 80 °C (Measuring coil)
Altitude	< 2000 m
Permissible humidity (operation)	5 % ... 95 % (non-condensing)

Approvals

UKCA

Certificate	UKCA-compliant
-------------	----------------

CMIM

Certificate	CMIM-compliant
-------------	----------------

UL, USA/Canada

Identification	UL 61010 Recognized
Note	Measuring coil

Standards and regulations

Standards/regulations	IEC 61010-2-030
	IEC 61869-10

PACT RCP-D190-10M - Coil



2910324

<https://www.phoenixcontact.com/in/products/2910324>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/2910324>



cUL Recognized

Approval ID: FILE E 357804



UL Recognized

Approval ID: FILE E 357804

cULus Recognized

PACT RCP-D190-10M - Coil

2910324

<https://www.phoenixcontact.com/in/products/2910324>



Classifications

ECLASS

ECLASS-11.0	27210992
ECLASS-12.0	27210992
ECLASS-13.0	27210992

ETIM

ETIM 9.0	EC002498
----------	----------

UNSPSC

UNSPSC 21.0	39121000
-------------	----------

PACT RCP-D190-10M - Coil

2910324

<https://www.phoenixcontact.com/in/products/2910324>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

PACT RCP-D190-10M - Coil

2910324

<https://www.phoenixcontact.com/in/products/2910324>



Accessories

PACT RCP-CLAMP - Holder

2904895

<https://www.phoenixcontact.com/in/products/2904895>



The optional holding device ensures the Rogowski coil is securely seated on busbars with a thickness of 10 ... 15 mm. During installation, the coil housing is pushed onto the flange of the holding device and snaps in automatically.

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in