



Part Number : [399200302](#)


Product Description : 15.00mm Beau Eurostyle, Fixed Mount PCB Terminal Block, High Voltage, High Power 115A, 2 Circuits

Series Number : 39920

Status : Obsolete

Product Category : Terminal Blocks and Barrier Strip

Engineering Number : 92B0502



Documents & Resources

Drawings

[399200302_sd.pdf](#)

[PK-39920-002-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Terminal Blocks and Barrier Strip
Series	39920
Description	15.00mm Beau Eurostyle, Fixed Mount PCB Terminal Block, High Voltage, High Power 115A, 2 Circuits
Application	Wire-to-Board
Component Type	One Piece
Product Name	Eurostyle Fixed Mount
Type	PCB Terminal Blocks and Connectors
UPC	756054719954

Agency

UL	E48521
----	--------

Electrical

Current - Maximum per Contact	115.0A
Voltage - Maximum	600V

Physical

Circuits (Loaded)	2
Color - Resin	Black

Entry Angle	Horizontal
Flammability	94V-0
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Number of Rows	1
Orientation	Vertical
Panel Mount	No
PCB Retention	Yes
PC Tail Length	6.35mm
Pitch - Mating Interface	15.00mm
Pitch - Termination Interface	15.00mm
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Polarized to Mating Part	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	130°C
Termination Interface Style	Through Hole
Wire Size (AWG)	1, 2, 3, 4, 6, 8
Wire Size mm ²	10.00-35.00

Solder Process Data

Lead-Free Process Capability	Product not active
------------------------------	--------------------