

Product data sheet

Specifications



Acti9 IC100kp+ 2C (1 - 99000 lux) SMART programmable twilight switch

CCT15495

Main

range of product	Acti9
Product name	Acti9 IC
Product or component type	Programmable twilight switch with time switch function
Device short name	IC100kp+
Device application	Building
Provided equipment	twilight sensor outdoor
Load type	incandescent lamp: 2600 W halogen lamp: 2600 W non-corrected fluorescent tube: 2300 VA serial-compensated fluorescent tube: 2300 VA parallel compensated fluorescent lamp: 730 VA (80 µF) compact fluorescent lamp: 170 W < 2 W LED lamp: 30 W > 2 W LED lamp: 200 W
User language	English French Russian Spanish Italian Dutch Danish Croatian Hungarian Slovene Portuguese German Romanian Polish Swedish Norwegian Finnish Czech

Complementary

Number of channels	2
Maximum power consumption in W	0.8 W standby
[Ue] rated operational voltage	230 V AC +10 % -15 % at 50/60 Hz
Maximum switching current	10 A - 250 V AC pf = 0.6 16 A - 250 V AC pf = 1
Minimum switching current	10 mA 230 V AC 100 mA 24 V AC/DC
Electrical insulation class	Class II
Output type	Dry contact
Accuracy	+/- 0.25 s/day 25 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contacts type and composition	C/O
Maximum number of programming range	84
Function available	External input for override Holiday schedules Automatic winter/summer time changeover Time limited or permanent deactivation of on/off function Switch preselection
Control type	By brightness detection By time schedule
control button type	4 push-buttons
Display type	Backlit LCD
Information displayed on mobile app	Operating time counter (per channel) Time Day Output contact status Current program
Time delay range	0...59 min (on) 0...59 min (off)
Power reserve	10 years
Type of setting	Weekly programming
Light intensity adjustment	1...99000 lux
Connections - terminals	2 x 0.5...2.5 mm² screw terminals solid or flexible 1 x 2.5 mm² screw terminals solid or flexible with sleeve
Mounting support	TH35 DIN rail conforming to EN 60715
Height	92.6 mm
Width	45 mm
Depth	66.7 mm
Product weight	138 g
Overvoltage category	Class 3
Marking	CE

Environment

Ambient air temperature for operation	-25...55 °C
ambient air temp for storage/ transportation	-30...70 °C
Relative humidity	90 %, non-condensing
IP degree of protection	IP20
Standards	EN 60669-2-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.000 cm
Package 1 Width	10.000 cm
Package 1 Length	10.500 cm
Package 1 Weight	262.000 g
Unit Type of Package 2	S03

Number of Units in Package 2	22
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	6.225 kg

Contractual warranty

Warranty (in months)	18
----------------------	----

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Environmental Disclosure	Product Environmental Profile

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	51645430-ab03-4d5b-9ca4-cf8bc05b4a81
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer

 Lifetime extension	
Repair	No

Use Again

 Repack and remanufacture	
End of life manual availability	End of Life Information
Removable battery	No
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins