

## FEATURES

- Digital indication of temperature, time, day and date
- Alarm and countdown function
- Calendar with day display
- Accurate result
- Clock (can be switched between 12 and 24 hour format)

## RS PRO LCD Digital Thermometer, for Wall/Desk Use

RS Stock No.: 656-5660



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO digital thermometer features a clock with alarm and countdown function. It has °C/°F selectable display so you can switch between Celsius and Fahrenheit, with the temperature ranges from 0 to +50°C. This digital thermometer can sit on a surface for easy viewing or can be mounted to a wall. A digital thermometer can measure temperature to a decimal point rather than a whole number meaning its results are more accurate.

## General Specifications

<b>Thermometer Type</b>	Handheld
<b>Number of Temperature Inputs</b>	1
<b>Absolute Maximum Temperature Measurement</b>	50°C
<b>Temperature Scale</b>	Centigrade/Fahrenheit
<b>Display type</b>	LCD
<b>Operating Temperature</b>	0°C to +50°C
<b>Applications</b>	Food industry, Hygiene testing, Industrial maintenance, Heating & ventilation, Scientific research, Medical testing, General purpose temperature monitoring

## Electrical Specifications

<b>Battery Type</b>	CR2032 button cell
---------------------	--------------------

## Mechanical Specifications

<b>Dimensions</b>	111mm x 54.5mm x 17 mm
<b>Length</b>	111mm
<b>Width</b>	54.5mm
<b>Height</b>	17 mm

## Approvals

### Compliance/Certifications

CE, EN 61340, RoHS Certificate of Compliance

## Similar Products

Stock No.	Brand	Product Name	Thermometer Type	Absolute Maximum Temperature Measurement	Probe Type
123-3216	RS PRO	RS52 Data Acquisition Digital Thermometer	Handheld	+1300°C, +1999°F	K
123-3217	RS PRO	RS53-II Data Acquisition Digital Thermometer	Handheld	+1372 °C, +2501 °F	J, K

