

115.111.129.98KTSO...-PP-ASLinear-Kugellager-Einheiten

# Linear ball bearing and housing units

## KTSO30-PP-AS (Series KTSO...-PP-AS)

open design, with self-aligning linear ball bearing, contact seals on both sides

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

Fw	30 mm
H	60 mm
B	87 mm
L	142 mm
	6 Number of rows of balls
1)	Main load direction
A5	43,5 mm Tolerance: +/-0,01
B2	14,3 mm Dimension B2 on diameter Fw
G2	M10
H2	35 mm Tolerance: +0,008/-0,016
H5	9,7 mm
H6	34 mm
JB	68 mm Tolerance: +/-0,15
JL	106 mm Tolerance: +/-0,15 Dimension JL symmetrical to bearing length L.
K5	M8 For fixing screws to ISO 4762-8.8 If there is a possibility of settling, the screws should be secured against rotation.
K8	NIP5MZ Lubrication nipple Lubrication hole symmetrical to bearing length L.
L6	54 mm Dimension L6 symmetrical to bearing length L.
N1	8,4 mm
N3	15 mm

N <sub>4</sub>	2,5 x 5,3 mm	Centring hole to DIN 332 type A
T <sub>5</sub>	22 mm	
$\alpha$	57 °	
m	1550 g	Mass
	Basic load ratings in main load direction The basic load ratings are only valid for hardened (670 HV +165 HV) and ground shaft raceways.	
C <sub>meix</sub>	9600 N	Basic dynamic load rating
C <sub>0</sub> max	12000 N	Basic static load rating



