

## INTRODUCTION

Dormer's Sheet Metal drills are a range of high speed steels drills specifically designed for drilling thin sheet steel and panels

- Manufactured from a premium substrate and to high quality standards for consistent and reliable performance
- They are available in a number of standard sizes to suit common rivets, screws and bolts
- Double ended version (A119) also available to help reduce inventory and increase economy

## MATERIAL

Premium High Speed Steel (HSS)

- Manufactured from M2 to provide good hardness
- Retains a sharp cutting edge under extreme conditions
- Steam tempered to improve performance and reduce chance of built-up-edge



## **GEOMETRY**

Standard 120 degree Point

Provides easy penetration in hand held applications

Special Web


 A thin web at the point provides excellent self centering properties

Short Flute

Provides rigidity for hand held drilling of thin panels and sheet

No Body Clearance

 Increases stability during drilling and breakthrough to give a superior quality hole





A119 • Stub Drill - Double Ended

Sheet Metal Drill

A119 • 1.1 1.2

• 1.3 1.4 1.5 1.6 2.1 2.2 2.3 4.1 4.2 4.3 5.1 5.2 5.3 6.1 6.2 6.3 6.4 7.1 7.2 7.3 7.4 8.1 8.2

A119

HSS


DIN 1897 **1.25**XD

120°



N







3.30 - 5.10

d, Øh <sub>8</sub> mm	d <sub>1</sub> decimal Inch	I <sub>2</sub> mm	I <sub>1</sub>	A119
3.30	0.1299	11	49	A1193.3
3.60	0.1417	12	52	A1193.6
4.10	0.1614	14	55	A1194.1
4.20	0.1654	14	55	A1194.2
4.90	0.1929	17	62	A1194.9
5.10	0.2008	17	62	A1195.1