


Geberit Mapress Copper adaptor with male thread



Example image



APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For service water and process water
- For compressed air (oil purity class 0–3)

- For negative pressure
- For inert gases (e.g. nitrogen)
- For technical building systems, industry and shipbuilding

- Seal ring made of CIIR, black, up to $\varnothing \leq 54$ mm
- Seal ring made of EPDM, black, from $\varnothing > 54$ mm
- Pressing socket with transparent protection plug

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed up to $\varnothing \leq 54$ mm

TECHNICAL DATA

Product material Gunmetal / lead-free gunmetal

Art. no.	DN	d, $\varnothing$ mm	R	Product material	L cm	H cm
61701	10	12	3/8	Lead-free gunmetal	3.2	1.5
61745	10 / 15	12	1/2	Gunmetal	3.6	1.9
61702	12 / 10	15	3/8	Lead-free gunmetal	3.3	1.3
61703	12 / 15	15	1/2	Gunmetal	3.6	1.6
61714	12 / 20	15	3/4	Lead-free gunmetal	3.8	1.8

Art. no.	DN	d _ø mm	R _e	Product material	L cm	H cm
61704	15	18	1/2	Lead-free gunmetal	3.7	1.7
61705	15 / 20	18	3/4	Lead-free gunmetal	3.8	1.8
61715	20 / 15	22	1/2	Lead-free gunmetal	3.8	1.7
61707	20	22	3/4	Lead-free gunmetal	3.9	1.8
61716	20 / 25	22	1	Lead-free gunmetal	4.1	2
61717	25 / 20	28	3/4	Lead-free gunmetal	4.2	1.9
61708	25	28	1	Lead-free gunmetal	4.3	2
61718	25 / 32	28	1 1/4	Lead-free gunmetal	4.4	2.1
61719	32 / 25	35	1	Lead-free gunmetal	4.8	2.2
61709	32	35	1 1/4	Lead-free gunmetal	4.9	2.3
61721	40 / 32	42	1 1/4	Lead-free gunmetal	5.8	2.8
61710	40	42	1 1/2	Lead-free gunmetal	5.8	2.8
61711	50	54	2	Lead-free gunmetal	6.3	2.8

Art. no.	DN	d _ø mm	R "	Product material	L cm	H cm
61730	65	66.7	2 1/2	Lead-free gunmetal	9.7	4.7
61732	65	76.1	2 1/2	Gunmetal	10.1	4.8
61733	65 / 80	76.1	3	Lead-free gunmetal	10.6	5.3
61734	80	88.9	3	Gunmetal	11	5