





PLP1.5I-C



- For indoor use
- *Wingless* design allows tie to be used in confined spaces
- Cable tie, mount, and fastener in a single part
- Economical push mount ties are used to attach bundles to another surface such as a flat panel
- Anchor is easily pressed into a pre-formed hole and locks in place
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation

■ Part Number	PLP1.5I-C
■ RoHS Compliancy Status	Compliant
■ Part Description	Push Mount Tie, 6.1", Intermediate cross section
■ Product Type	Cable Ties
■ Material	Nylon 6.6
■ Color	Natural
■ CSA Certified	Yes
■ UL Listed (File #E56854)	No
■ UL Recognized (File #E56854)	Yes
■ Length (In.)	6.1
■ Length (mm)	156
■ Width (In.)	.135
■ Width (mm)	3.4
■ CE Compliant	Yes
■ Cross Section	Intermediate
■ Head Height (In.)	.236
■ Head Height (mm)	6.0
■ Locking Style	Locking
■ Material Flammability Rating	UL 94V-2
■ Max. Bundle Diameter (In.)	1.25
■ Max. Bundle Diameter (mm)	32
■ Max. Continuous Use Temperature	185°F (85°C)
■ Max. Panel Thickness (In.)	.093
■ Max. Panel Thickness (mm)	2.4
■ Min. Loop Tensile Strength (Lbs.)	40
■ Min. Loop Tensile Strength (N)	178

■ Nominal Hole Diameter (In.)	.187
■ Nominal Hole Diameter (mm)	4.7
■ Pricing Description	Push Mount Tie, 6.1"L (156mm), Intermediate, Nylon, Natural
■ Thickness (In.)	.045
■ Thickness (mm)	1.1
■ Tool	GTS, GTSL, GS2B, PTS, PPTS, STS2
■ Min. Order UOM	PC
■ Min. Order Qty.	100
■ BOM Qty. (# of Pkgs.)	



PANDUIT* PART NO.	BUNDLE DIA.		A	B	C	D	E	F	G	H	MAX PANEL THICKNESS in (mm)	MIN. LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT 100 pcs lbs (g)
	MAX. in (mm)	MIN. in (mm)												
PLP1.51	.06 (1.5)	1.25 (31.8)	.045 (1.1)	.135 (3.4)	.350 (8.9)	.236 (6.0)	.270 (6.9)	6.13 (156)	.260 (6.6)	.187 (4.7)	.093 (2.4)	40 (178)	INTERMEDIATE	.17 (77)

NOTE:

- *1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
- 2) THESE PARTS ARE RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.
- 3) SEE DRAWING SS-26803(A) FOR PLP1S, PLP1.5S & PLP2S.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

STRAP, PUSH MOUNT - PLP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .1(2.5) (.XXX) ± .020 (.51)
(.XX) ± .02(.5) ANGLES ± -----

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
RAM

DATE
2-1-94

CHK'D
HVP

MAT'L:

NYLON 6.6

SCALE

DRAWING NO.

SS-26888

DWG
A
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
---	----	---		REVISED HEAD ON TIE, DOES NOT HAVE THE LEDGE ON TOP VIEW OF HEAD	----	---		
3	1/29/04	JABO		CHANGED FORMAT FOR CONSISTENCY SEE ECN FOR DETAILS	26888	3		