

Spiral Cable Gland

Features


- Spiral Glands form the range of cable management are the ideal way to protect cable connections
- These general use spiral option provide extra strain relief and flexibility when bending, along with added protection and higher resistance to wear and tear
- Its simple screw on action can help reduce assembly time, and is idea for use with hand held and portable devices



Specification

IP Rating	IP68
With Strain Relief	Yes
Model	Straight
Material	Polyamide
Glass-Fibre Reinforced	No
Shock Resistant	Yes
Bend Radius Protection / Trumpet Flare	Yes
With Locknut	Yes
Snapping in Opening	Yes
Flat Cable Coupling	No
Explosion-Tested Version	No
For Armoured Cable	No
EMC-Version	No
Screened	No
Type of Sealing	Sealing Ring
For Ex-Zone Gas	None
For Ex-Zone Dust	None
Halogen Free	Yes
Operating Temperature	-40 ... 100 °C

Dimensions



RND Type	AG	GL	Ød1	H	Thread Size	Thread Length	Colour	Colour Code	Cable Ø
RND 465-01280	25 mm	11 mm	20 mm	114 mm	M25	1 mm	Black	RAL 9005	13 ... 18 mm
RND 465-01281	18.6 mm	8 mm	10.5 mm	78 mm	PG11	8 mm	Black	RAL 9005	5 ... 10 mm
RND 465-01282	12.5 mm	8 mm	7 mm	54 mm	PG7	8 mm	Black	RAL 9005	3 ... 6.5 mm
RND 465-01283	15.2 mm	8 mm	8.5 mm	63 mm	PG9	8 mm	Black	RAL 9005	4 ... 8 mm
RND 465-01284	20 mm	9 mm	13 mm	90 mm	M20	9 mm	Black	RAL 9005	6 ... 12 mm
RND 465-01285	20 mm	9 mm	13 mm	90 mm	M20	9 mm	Light Grey	RAL 7035	6 ... 12 mm
RND 465-01286	12 mm	8 mm	7 mm	54 mm	M12	8 mm	Black	RAL 9005	3 ... 6.5 mm
RND 465-01287	16 mm	8 mm	8.5 mm	63 mm	M16	8 mm	Light Grey	RAL 7035	3 ... 6.5 mm
RND 465-01288	18.6 mm	8 mm	10.5 mm	78 mm	PG11	8 mm	Light Grey	RAL 7035	5 ... 10 mm
RND 465-01289	16 mm	8 mm	8.5 mm	63 mm	M16	8 mm	Black	RAL 9005	4 ... 8 mm
RND 465-01290	12 mm	8 mm	7 mm	54 mm	M12	8 mm	Light Grey	RAL 7035	3 ... 6.5 mm
RND 465-01291	25 mm	11 mm	20 mm	114 mm	M25	1 mm	Light Grey	RAL 7035	13 ... 18 mm
RND 465-01294	15.2 mm	8 mm	8.5 mm	63 mm	PG9	8 mm	Light Grey	RAL 7035	4 ... 8 mm
RND 465-01296	12.5 mm	8 mm	7 mm	54 mm	PG7	8 mm	Light Grey	RAL 7035	3 ... 6.5 mm