

SCALANCE X201-3PIRT managed IE IRT switch, 1x 10/100 Mbit/s RJ45 ports, 3x 100 Mbit/s POF SC RJ ports, Error signaling contact with set button, Redundant power supply, PROFINET IO device, network management, Redundancy Manager integrated, incl. electron. manual on CD-ROM, C-plug optional



<b>Product type designation</b>	<b>SCALANCE X201-3P IRT</b>
<b>Transfer rate</b>	
Transfer rate	10 Mbit/s, 100 Mbit/s
<b>Interfaces / for communication / Integrated</b>	
Number of electrical connections	
<ul style="list-style-type: none"> <li>for network components or terminal equipment</li> </ul>	1
number of 100 Mbit/s SC-RJ-ports / for POF FOC	
<ul style="list-style-type: none"> <li>with push-pull connection system</li> </ul>	3
<b>Interfaces / other</b>	
Number of electrical connections	
<ul style="list-style-type: none"> <li>for signaling contact</li> </ul>	1
<ul style="list-style-type: none"> <li>for power supply</li> </ul>	1
<ul style="list-style-type: none"> <li>for redundant voltage supply</li> </ul>	1
Type of electrical connection	
<ul style="list-style-type: none"> <li>for signaling contact</li> </ul>	2-pole terminal block
<ul style="list-style-type: none"> <li>for power supply</li> </ul>	4-pole terminal block
design of the removable storage	
<ul style="list-style-type: none"> <li>C-PLUG</li> </ul>	Yes

Signal inputs/outputs	
Operating voltage / of the signaling contacts	
<ul style="list-style-type: none"> <li>at DC / Rated value</li> </ul>	24 V
Operating current / of the signaling contacts	
<ul style="list-style-type: none"> <li>at DC / maximum</li> </ul>	0.1 A
Supply voltage, current consumption, power loss	
Type of voltage / of the supply voltage	DC
Supply voltage	
<ul style="list-style-type: none"> <li>external</li> </ul>	24 V
<ul style="list-style-type: none"> <li>external / minimum</li> </ul>	18 V
<ul style="list-style-type: none"> <li>external / maximum</li> </ul>	32 V
Product component / fusing at power supply input	Yes
Fuse protection type / at input for supply voltage	1.1 A / 33 V
Consumed current / maximum	0.35 A
Power loss [W]	
<ul style="list-style-type: none"> <li>at DC / at 24 V</li> </ul>	8.4 W
Ambient conditions	
Ambient temperature	
<ul style="list-style-type: none"> <li>during operation</li> </ul>	-25 ... +50 °C
<ul style="list-style-type: none"> <li>during storage</li> </ul>	-40 ... +70 °C
<ul style="list-style-type: none"> <li>during transport</li> </ul>	-40 ... +70 °C
Relative humidity	
<ul style="list-style-type: none"> <li>at 25 °C / without condensation / during operation / maximum</li> </ul>	95 %
Protection class IP	IP30
Design, dimensions and weights	
Design	compact
Width	60 mm
Height	125 mm
Depth	124 mm
Net weight	0.78 kg
Mounting type	
<ul style="list-style-type: none"> <li>35 mm DIN rail mounting</li> </ul>	Yes
<ul style="list-style-type: none"> <li>wall mounting</li> </ul>	Yes
<ul style="list-style-type: none"> <li>S7-300 rail mounting</li> </ul>	Yes
<ul style="list-style-type: none"> <li>S7-1500 rail mounting</li> </ul>	No
Product features, product functions, product components / general	
Cascading in the case of a redundant ring / at reconfiguration time of $<\sim 0.3\sim$ s	50
Cascading in cases of star topology	any (depending only on signal propagation time)

## Product functions / management, configuration, engineering

Product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• Configuration with STEP 7	Yes
• Port mirroring	No
• multiport mirroring	No
• with IRT / PROFINET IO switch	Yes
• PROFINET IO diagnosis	Yes
PROFINET conformity class	C
Product function / switch-managed	Yes
Protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	No
• DCP	Yes
• LLDP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
Identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 – higher-level designation/location designation	Yes

## Product functions / Diagnostics

Product function	
• Port diagnostics	Yes
• Statistics Packet Size	Yes
• Statistics packet type	Yes
• Error statistics	Yes

## Product functions / DHCP

Product function	
• DHCP client	Yes

## Product functions / redundancy

Product function	
------------------	--

• Ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
Protocol / is supported / Media Redundancy Protocol (MRP)	Yes
Product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• Media Redundancy Protocol for Planned Duplication (MRPD)	Yes
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
• Passive listening	Yes

#### Product functions / Security

Protocol / is supported	
• SSH	Yes

#### Product functions / time

Product function	
• SICLOCK support	Yes
Protocol / is supported	
• NTP	No
• SNTP	Yes

#### Standards, specifications, approvals

Standard	
• for FM	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4
• for hazardous zone	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
• for safety / from CSA and UL	UL 60950-1, CSA C22.2 No. 60950-1
• for hazardous zone / from CSA and UL	ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T4
• for emitted interference	EN 61000-6-4 (Class A)
• for interference immunity	EN 61000-6-2

#### Standards, specifications, approvals / CE

Certificate of suitability / CE marking	Yes
---	-----

#### Standards, specifications, approvals / other

Certificate of suitability	EN 61000-6-2, EN 61000-6-4
----------------------------	----------------------------

- C-Tick
- Railway application in accordance with EN 50155
- Railway application in accordance with EN 50124-1
- KC approval

Yes  
No  
No  
Yes

#### Standards, specifications, approvals / Product conformity

MTBF 78.03 y

#### accessories

Product extension / optional / C-PLUG Yes

#### Further information / Internet-Links

##### Internet-Link

- to website: Selector SIMATIC NET SELECTION TOOL
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<http://www.siemens.com/snst>  
  
<http://www.siemens.com/simatic-net>  
<https://mall.industry.siemens.com>  
<http://www.siemens.com/industry/infocenter>  
<http://automation.siemens.com/bilddb>  
<http://www.siemens.com/cax>  
<https://support.industry.siemens.com>

#### Security information

##### Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

12/17/2019