

Dust Extractor XGT®

VC003GL

40Vmax • 230 mbar • 15 L • L

XGT® Battery powered Wet/dry dust extractor for cleaning.

A versatile wet/dry dust extractor that runs on with XGT® battery. The batteries can be connected in parallel. It Matches filter class 'L'. Tank capacity is 15 L which enables continuous cleaning work.



Technical specifications

Vacuum hose length	1,7 m
Vacuum hose diameter	32 mm
Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Air volume	3,2 m³/min
Max. sealed suction	230 mbar
Suction power	310 W
Continuous Use XGT® 40V Max / 5.0 Ah X2	28 - 220 min
Tank Capacity for Dust	15 L
Tank Capacity for Liquids	12 L
Product net weight	7,8 kg
Sound Pressure Level (L _{pA})	≤ 70 dB(A)
Noise Uncertainty (K Factor)	2,5 dB(A)
Tool weight with battery	8,4 - 11,5 kg
Product Dimensions (L x W x H):	366 x 334 x 475

User benefits

- Carry handle for easy transportation
- Quiet operation for operator comfort
- For both wet and dry vacuum cleaning
- Flat top design for space saving in storage
- Approved for Dust Class L in accordance with the EU standard
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

■ Optional AC

191V67-2

Water Filter Set



■ Other

User manual

Parts drawing