





ITEM #	PART #	REV	DESCRIPTION	QTY	Material	Weight
1	MNZ028	03	Nozzle Body	1	Mild Steel	13.3g
2	FPZ006	03	Compression spring	1	Music Wire	0.2g
3	MZZ011	05	Nozzle seat	1	Aluminium	0.7g
4	HAZ002	03	5mm ball bearing	1	Chrome Steel	0.5g
5	MNZ013	03	2 Hole nozzle tip	1	Mild Steel	11.0g



SECTION A-A

 THIS DRAWING AND THE INFORMATION IT CONTAINS IS THE PROPERTY OF POWER ADHESIVES AND IS CONFIDENTIAL. IT MUST NOT BE REPRODUCED EITHER WHOLLY OR IN PART. ALL RIGHTS IN RESPECT OF PATENTS, DESIGNS AND COPYRIGHTS ARE RESERVED.	MATERIAL		DRAWN	SteveE	DIMENSIONS ARE IN MM UNLESS OTHERWISE STATED  THIRD ANGLE	TOLERANCES UNLESS OTHERWISE STATED WHOLE NUMBERS ±0.5mm 1 DECIMAL PLACE ±0.3mm 2 DECIMAL PLACE ±0.1mm	SCALE 1:1
	FINISH		DATE	12/07/2016			SHEET 1 OF 2
	COLOUR		ECR No.		TITLE		2 Hole Nozzle
	NOTES						
						DWG. No.	MPN - ADJ015
					A4		01

	1	2	3	4	5	6				
A	Technical data									
	Type	Hot melt applicator nozzle								
	Material composition	Aluminium, steel, music wire								
	Weight	25.7g (0.90 oz)								
	Thread size	5/16 UNF								
	Nozzle hole size	2 x 1.5mm (0.08")								
	Spring rate	0.48 N/mm (2.75 lb/inch)								
B										
C										
D	 THIS DRAWING AND THE INFORMATION IT CONTAINS IS THE PROPERTY OF POWER ADHESIVES AND IS CONFIDENTIAL. IT MUST NOT BE REPRODUCED EITHER WHOLLY OR IN PART. ALL RIGHTS IN RESPECT OF PATENTS DESIGNS AND COPYRIGHTS ARE RESERVED.		MATERIAL		DRAWN	SteveE	DIMENSIONS ARE IN MM UNLESS OTHERWISE STATED  THIRD ANGLE	TOLERANCES UNLESS OTHERWISE STATED WHOLE NUMBERS ±0.5mm 1 DECIMAL PLACE ±0.3mm 2 DECIMAL PLACE ±0.1mm	SCALE 1:1	
			FINISH		DATE	12/07/2016			SHEET 2 OF 2	
			COLOUR		ECR No.					
			NOTES			TITLE				
						2 Hole Nozzle				
			DWG. No.		ADJ015	REVISION	01			
			1	2	3	4	5	6		