




PIDG

TE Internal #: 326875  
Closed Ring Tongue Terminal, 26 – 22 AWG, #6 / M3.5 Stud, 3.68 mm [.145 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, PIDG

[View on TE.com >](#)

Terminals & Splices > Ring Terminals > PIDG Ring Tongue Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 202 – 810 CMA

Stud Size: #6, M3.5

[All PIDG Ring Tongue Terminals \(410\)](#)

Features

Product Type Features

|                                        |                             |
|----------------------------------------|-----------------------------|
| Terminal Features                      | Inspection Slot             |
| Ring Terminal Product Type             | Closed Ring Tongue Terminal |
| Stud Size                              | #6, M3.5                    |
| Sealable                               | No                          |
| Wire Insulation Support Retention Type | Insulation Support          |

Configuration Features

|                 |   |
|-----------------|---|
| Number of Holes | 1 |
|-----------------|---|

Electrical Characteristics

|                |       |
|----------------|-------|
| Voltage Rating | 300 V |
|----------------|-------|

Body Features

|                |        |
|----------------|--------|
| Product Weight | .322 g |
|----------------|--------|

Contact Features

|             |        |
|-------------|--------|
| Barrel Type | Closed |
|-------------|--------|



|                           |          |
|---------------------------|----------|
| Terminal Orientation      | Straight |
| Terminal Plating Material | Tin      |

Mechanical Attachment

|                         |      |
|-------------------------|------|
| Wire Insulation Support | With |
|-------------------------|------|

Dimensions

|                                      |                               |
|--------------------------------------|-------------------------------|
| Wire Size                            | 202 – 810 CMA                 |
| Stud Diameter                        | 3.68 mm[.145 in]              |
| Tongue Thickness                     | .79 mm[.031 in]               |
| Product Length                       | 18.8 mm[.74 in]               |
| Compatible Insulation Diameter (Max) | 2.08 mm[.082 in]              |
| Compatible Insulation Diameter Range | 1.27 – 2.08 mm[.05 – .082 in] |

Usage Conditions

|                   |                     |
|-------------------|---------------------|
| Insulation Option | Partially Insulated |
|-------------------|---------------------|

Operation/Application

|                                       |        |
|---------------------------------------|--------|
| Compatible With Wire Base Material    | Copper |
| Compatible With Wire Plating Material | Tin    |

Industry Standards

|                               |    |
|-------------------------------|----|
| Government Qualified Terminal | No |
|-------------------------------|----|

Packaging Features

|                    |             |
|--------------------|-------------|
| Packaging Quantity | 500         |
| Packaging Method   | Loose Piece |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC                                                |



Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 59275  
T-HEAD PIDG PG SH 26-20 ASSY

TE Part # 46121  
DAHT PG PIDG 26-22 ASSY

TE Part # 69344  
PIDG 26-22 DIE SET

Also in the Series | PIDG

Compression Connectors(17)

Crimp Wire Pins, Tabs & Ferrules(41)

Knife Disconnects(11)

Quick Disconnects(38)

Ring Terminals(588)

Spade Terminals(228)

Special Purpose Terminals(1)

Splices(41)

Customers Also Bought








TE Part #1617002-9  
B07A235BC1 = B07 10 AMP FULL S



TE Part #146368N001  
502K026/S(C40)



TE Part #3-644457-5  
05P MTA100 HDR ASSY R/A NARROW




TE Part #2-2308348-0  
CRIMP FLANGE 10 LARGE



TE Part #4-1393766-1  
R10-E1Y2-V2.5K=R10



TE Part #35189  
SPLICE,SOLIS BUTT 2



TE Part #36957  
SPLICE,SOLIS BUTT 1/0



TE Part #9-1437470-0  
SSC12ALA=120VAC 50/60HZ 20S TO



TE Part #1-1393771-6  
JWD-171-24=REED RELAYS

TE Part #7218310001  
RPS-2.5K-18-12/2.0-S1-9

Documents

Product Drawings  
TERMINAL,PIDG R 26-22 6

English

CAD Files  
3D PDF

3D

Customer View Model  
ENG\_CVM\_CVM\_326875\_W.2d\_dxf.zip

English

Customer View Model  
ENG\_CVM\_CVM\_326875\_W.3d\_igs.zip

English

Customer View Model  
ENG\_CVM\_CVM\_326875\_W.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



PIDG TERMINALS & SPLICES Quick Reference Guide

English