

## FEATURES

- Flexible and durable cable with PVC sheath
- Fully moulded connectors for strength and durability
- Reliable integrated strain relief for connection support and protection
- BS 1363 3-pin plug with 13 A fuse
- Right angled 10 A IEC C13 socket

# RS PRO 2m Power Cable, C13, IEC to UK Plug, 10 A, 250 V

RS Stock No.: 426-395



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

From RS Pro a high quality and durable power cable assembly or power cord for connecting an appliance to a mains power supply. This power cord is fully equipped with a UK BS1363 3 pin mains plug on one end and an IEC C13 type connector on the other that connects to the appliance. The power lead features integrated strain reliefs that provide additional protection and support to the connectors and prevent damage caused by excessive bending

## General Specifications

<b>Connector A</b>	C13, IEC
<b>Connector B</b>	UK Plug
<b>Sheath Colour</b>	White
<b>Connector A Type</b>	CEE 7/7
<b>Mains Plug Type</b>	Type G – British BS1363
<b>Mains Socket Type</b>	IEC 60320 C13
<b>Connector B Type</b>	CEE 7/7
<b>Fire Behaviour</b>	Flame Retardant
<b>Outer Sheath Material</b>	PVC
<b>Connector A Angle</b>	Straight
<b>Connector B Angle</b>	Right Angle
<b>Connector A Gender</b>	Female
<b>Connector B Gender</b>	Male
<b>Terminals</b>	Brass
<b>Conductor</b>	3 Wire
<b>Applications</b>	DIY and home improvements Maintenance work Household entertainment (TVs, satellite boxes, routers etc.) Industrial machines and equipment Office desks (Monitors, computers, phones) Any electrical device needed to be powered by the mains

## Electrical Specifications

<b>Current Rating</b>	10A
<b>Voltage Rating</b>	250V
<b>Insulation Resistance</b>	>10MΩ
<b>Cable Retention</b>	0.5mm <sup>2</sup> -1mm <sup>2</sup> >30N 1.25mm <sup>2</sup> -1.5mm <sup>2</sup> >60N
<b>Electrical Strength</b>	2.5kV 50Hz
<b>Safety Test</b>	4.4kV 50Hz
<b>Capacitance</b>	95.08pF/m
<b>Inductance</b>	0.43μH/m

## Mechanical Specifications

<b>Length</b>	15m
<b>Cross Sectional Area</b>	7mm
<b>Weight</b>	175g
<b>Withdrawal Force</b>	10N-50N
<b>Gauge</b>	1.5mm <sup>2</sup>
<b>Copper Wire Stranding</b>	48 Strands of 0.202mm <sup>2</sup>

## Operation Environment Specifications


<b>Maximum Pin Temperature</b>	65°C
--------------------------------	------

## Approvals

<b>Compliance/Certifications</b>	CE / UR / cUR
<b>Standards Met</b>	IEC 60320




ASSEMBLY :



Notes :

1. ALL DIMENSIONS IN mm.
2. PLUG AND CONNECTOR MARKING :  
REFER TO MARKING DRAWING NO. : VP-0401 AND VC-0402 RESPECTIVELY.
3. PLUG AND CONNECTOR DETAILS :  
REFER TO PRODUCT DRAWING NO. : P-0013 AND C-0063 RESPECTIVELY.
4. THIS PART CAN BE MANUFACTURED AT ANY LOCATION WHICH HAS SAFETY APPROVAL.



CABLE CUTTING

CABLE SOURCE :

1. BAO HING(SHENZHEN).
2. TONG YUAN(SHENZHEN).
3. TA HSING(SHENZHEN).