

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19

© COPYRIGHT 1994

BY AMP INCORPORATED. ALL RIGHTS RESERVED.





LOC

DIST

REVISIONS


P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
0		RELEASED	FJ00-3023-95	7/31'95	TS	AT
A		REVISED	FJ00-0253-97	2/20'97	TH	KY
B		REVISED	FJ00-2055-98	27OCT98	TH	KY

— 1 ; 本図



SECT. B-B

SECT. C-C



注 :

1. 適用圧着規格番号 : 114-5193

NOTES;

1. APPLICABLE CRIMPING SPEC No. 114-5193

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN T. SHINOHARA 7/31'95		WIRE RANGE 適合電線断面積 AWG #22-#20 (0.3-0.5mm)		INSULATION DIA 被覆外径 1.4-1.7	
CHK K. YUASA 7/31'95		APVD A. TOMITA 7/31'95		AMP 株式会社アール・ピー・エー Kawasaki, Japan			
DIMENSIONS 単位 ㎜		TOLERANCES UNLESS OTHERWISE SPECIFIED 一般公差 10% : ±0.2 30% : ±0.25 100% : ±0.3 ANGLE : ±0.3°		PRODUCT SPEC 製品規格 —		NAME 名称 REC CONTACT (MINI MULTI LOCK CONN)	
MATERIAL 材料 PRE-TIN 錫メッキ鋼線 0.2t		FINISH 仕上 —		APPLICATION SPEC 取付適用規格 —		WEIGHT 0.16g	
				SIZE A3		CAGE CODE 00779	
				DRAWING NO C-917308		SCALE 10-1	
				SHEET 1		OF 1	
				REV B		参考図面	

参考図面