

CA-06P1N122S00X - Device connector front mounting



1243931

<https://www.phoenixcontact.com/in/products/1243931>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector front mounting, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Pin, Solder connection, Flat gasket, 4x Ø 3.2, flange dimensions: 25 mm x 25 mm, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires

Commercial data

Item number	1243931
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	ABRAEL
GTIN	4063151405953
Weight per piece (including packing)	31.5 g
Weight per piece (excluding packing)	31 g
Customs tariff number	85366990
Country of origin	DE

CA-06P1N122S00X - Device connector front mounting



1243931

<https://www.phoenixcontact.com/in/products/1243931>

Technical data

Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

Connector

Insulating body

Coding	N
Insulation body material	PBT
Contact material	CuZn
Contact surface material	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Pin
Application	Signal
Number of positions	6
Direction of rotation	Standard
Connection profile	6
Rated voltage	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Contact diameter Signal contacts	2 mm
Litz wire cross-section Signal contacts max.	2.5 mm ²
Nominal current per signal contact	20 A

Housing

Housing material	GD-Zn
Flange dimensions	25 mm x 25 mm
Type of locking	for standard and SPEEDCON interlock
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23


Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Drawings

Schematic diagram



Connector pin assignment

CA-06P1N122S00X - Device connector front mounting





1243931

<https://www.phoenixcontact.com/in/products/1243931>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1243931>

 cUL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	10 A	14	-

 UL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	20 A	14	-

cULus Recognized				
-------------------------	--	--	--	--

CA-06P1N122S00X - Device connector front mounting



1243931

<https://www.phoenixcontact.com/in/products/1243931>

Classifications

ECLASS

ECLASS-11.0	27371392
ECLASS-12.0	27371392
ECLASS-13.0	27371392

ETIM

ETIM 9.0	EC002498
----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

1243931

<https://www.phoenixcontact.com/in/products/1243931>

Accessories

SF-Z0019 - Protective cap

1607449

<https://www.phoenixcontact.com/in/products/1607449>



Plastic protection cap, with eye, IP40 for connectors with M23 external thread, RF, SF series

RC-Z2104X - Metal protective cap

1241739

<https://www.phoenixcontact.com/in/products/1241739>



Metal protective cap, series: RC, UC, RF, SF, NC, RM, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

CA-06P1N122S00X - Device connector front mounting



1243931

<https://www.phoenixcontact.com/in/products/1243931>

RC-Z2068X - Metal protective cap

1241735

<https://www.phoenixcontact.com/in/products/1241735>

Metal protective cap, series: RC, UC, RF, SF, NC, RM, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)



CA-Z0120 - Color coding

1620704

<https://www.phoenixcontact.com/in/products/1620704>

Color coding, color: green



CA-06P1N122S00X - Device connector front mounting



1243931

<https://www.phoenixcontact.com/in/products/1243931>

CA-Z0121 - Color coding

1620705

<https://www.phoenixcontact.com/in/products/1620705>

Color coding, color: orange



CA-Z0122 - Color coding

1620706

<https://www.phoenixcontact.com/in/products/1620706>

Color coding, color: black



CA-06P1N122S00X - Device connector front mounting



1243931

<https://www.phoenixcontact.com/in/products/1243931>

CA-Z0001 - Contact removal tool

1620699

<https://www.phoenixcontact.com/in/products/1620699>



Unlocking tool for contact carriers for snapping in the M23 signal device connectors

PROT-M23PRO-OT-IP20 - Plastic protective cap

1055753

<https://www.phoenixcontact.com/in/products/1055753>



Plastic protective cap, M23, series: M23 PRO

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in