

1-172159-9 ✓ ACTIVE

MATE-N-LOK | Mini-Universal MATE-N-LOK


TE Internal #: 1-172159-9

4 Position, Cap, Housing, Crimp, Wire-to-Panel / Wire-to-Wire, UL 94V-0, 4.2 mm [.165 in] Centerline, 2 Row, 600 VAC, Mini-Universal MATE-N-LOK

[View on TE.com >](#)



Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**

Connector & Housing Type: **Cap**

Termination Method to Wire & Cable: **Crimp**

Connector System: **Wire-to-Panel, Wire-to-Wire**

Contact Retention Within Housing: **Without**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Cap
Connector System	Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	2

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

--	--



Multiple Contact Types	Without
Contact Retention Within Housing	Without
Contact Type	Pin

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	With
Panel Mount Feature Type	Mounting Ears
Connector Mounting Type	Panel Mount

Housing Features

Centerline (Pitch)	4.2 mm[.165 in]
Housing Material	Nylon 66

Dimensions

Panel Thickness (Recommended)	.8 – 2 mm[.031 – .078 in]
Connector Width	9.8 mm
Connector Height	9.8 mm
Connector Length	11.8 mm
Row-to-Row Spacing	4.2 mm[.165 in]

Usage Conditions

Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
CSA Rating	Certified, LR 7189
UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	500
Packaging Method	Bag



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






Also in the Series | **Mini-Universal MATE-N-LOK**





Insertion & Extraction Tools(1)



PCB Headers & Receptacles(93)



Power Contacts(89)




Rectangular Power Connectors(196)




Wire-to-Board Headers & Receptacles (93)

Customers Also Bought



TE Part #811134-000
202D221-12-0



TE Part #808083-000
222D932-12-0



TE Part #F07599-000
MP-508254-5-8A



TE Part #32947
PG R 22-16 COMM 22-18 MIL 6



TE Part #34484
TERMINAL,SOLIS R 14-12 10



TE Part #1-172159-2
MINI UNIVERSAL M-N-L CAP 4P




TE Part #1-172332-9
MUMNLM CAP 9P



TE Part #6-1437558-9
MTE106E=(MSTE) SW TOG
WATERPRO



TE Part #1744036-6
06P ECONOMY POWER .200 CL HSG



TE Part #1466110-1
13201140002

Documents



Product Drawings

MINI UNIVERSAL M-N-L CAP 4P

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-172159-9_M.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-172159-9_M.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-172159-9_M.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Engineering Report

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English