

Product data sheet

Characteristics

C25V36M150

circuit breaker ComPacT NSX250HB1, 75 kA at 690 VAC, MicroLogic 6.2 E-M trip unit 150 A, 3 poles 3d



Main

| | |
|--|--|
| Range | ComPacT new generation |
| Product name | ComPacT NSX new generation |
| Device short name | NSX250HB1 |
| Product or component type | Circuit breaker |
| Device application | Motor protection |
| Poles description | 3P |
| Protected poles description | 3D |
| [In] rated current | 150 A at 65 °C |
| [Ue] rated operational voltage | 690 V AC 50/60 Hz |
| Network type | AC |
| Network frequency | 50/60 Hz |
| Suitability for isolation | Yes conforming to EN/IEC 60947-2 |
| Utilisation category | Category A |
| [Icu] rated ultimate short-circuit breaking capacity | 85 KA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 80 KA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 75 KA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 |
| Performance level | HB1 75 kA 690 V AC |
| Trip unit name | Micrologic 6.2 E-M |
| Trip unit technology | Electronic |
| Trip unit protection functions | LSIG |
| Control type | Toggle |
| Circuit breaker mounting mode | Fixed |

Complementary

| | |
|---|--|
| [Ui] rated insulation voltage | 800 V AC 50/60 Hz |
| [Uimp] rated impulse withstand voltage | 8 kV |
| [Ics] rated service short-circuit breaking capacity | 85 KA at 500 V AC 50/60 Hz conforming to IEC 60947-2 80 KA at 525 V AC 50/60 Hz conforming to IEC 60947-2 75 KA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 |
| Mechanical durability | 20000 cycles |
| Electrical durability | 20000 Cycles at 440 V In/2 10000 Cycles at 440 V In 10000 Cycles at 690 V In/2 5000 cycles at 690 V In |
| Power dissipation per pole | 6.3 W |
| Mounting support | Backplate |
| Mounting position | Horizontal and vertical Flat on the back |
| Upside connection | Front |
| Downside connection | Front |
| Connection pitch | 35 mm |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|---|---|
| Protection type | L : for overload protection (long time) So : for short time short-circuit protection I : for instantaneous short-circuit protection G : for ground fault protection |
| Trip unit rating | 150 A at 65 °C |
| Motor tripping class | 30 20 10 5 |
| Complementary motor protection | Phase unbalance Underload Protracted starting time Stalled rotor |
| Long-time pick-up adjustment type Ir (thermal protection) | Adjustable 9 settings |
| [Ir] long-time protection pick-up adjustment range | 70...150 A |
| Long-time protection delay adjustment type tr | Adjustable |
| [tr] long-time protection delay adjustment range | 120 S at 1.5 x Ir for trip class 5 6.5 S at 6 x Ir for trip class 5 5 S at 7.2 x Ir for trip class 5 240 S at 1.5 x Ir for trip class 10 13.5 S at 6 x Ir for trip class 10 10 S at 7.2 x Ir for trip class 10 480 S at 1.5 x Ir for trip class 20 26 S at 6 x Ir for trip class 20 20 S at 7.2 x Ir for trip class 20 720 S at 1.5 x Ir for trip class 30 38 S at 6 x Ir for trip class 30 30 s at 7.2 x Ir for trip class 30 |
| Thermal memory | 20 minutes before and after tripping |
| Short-time protection pick-up adjustment type lsd | Adjustable |
| [lsd] Short-time protection pick-up adjustment range | 5...13 x Ir |
| Short-time protection delay adjustment type tsd | Fixed |
| Instantaneous protection pick-up adjustment type li | Fixed |
| [li] instantaneous protection pick-up adjustment range | 2250 A |
| Ground-fault protection pick-up adjustment type Ig | Adjustable 9 settings |
| [lg] ground-fault protection pick-up adjustment range | 0.2...1 x In Ig enable on/off |
| Ground-fault protection time delay adjustment type tg | Adjustable 5 settings |
| [tg] ground-fault protection time delay adjustment range | 0...0.4 s |
| Earth-leakage protection | Without |
| Zone selective interlocking ZSI | With |
| Number of slots for electrical auxiliaries | 5 slot(s) |
| Local signalling | Flashing LED (green) for ready to operate LED 95 % lth (red) for temperature over set point |
| Display type | LCD display |
| Type of measurement | Energy meter |
| Communication of data | Maximeters/Minimeters Time-stamped histories and event tables Protection and alarm settings Demand current and power Energy metering Power quality Thermal image function Maintenance indicators Instantaneous and demand values Phase sequence |
| Width (W) | 105 mm |
| Height (H) | 161 mm |
| Depth (D) | 86 mm |
| Net weight | 2.4 kg |

Environment

| | |
|---------------------------------------|--|
| Standards | EN/IEC 60947 |
| Product certifications | Marine CCC EAC |
| Overvoltage category | Class II |
| Electrical shock protection class | Class II |
| Pollution degree | 3 conforming to IEC 60664-1 |
| IP degree of protection | IP40 conforming to IEC 60529 |
| IK degree of protection | IK07 conforming to IEC 62262 |
| Ambient air temperature for operation | -25...70 °C |
| Ambient air temperature for storage | -40...85 °C |
| Relative humidity | 0...95 % |
| Operating altitude | 0...2000 m without derating 2000 m...5000 m with derating |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 14.0 cm |
| Package 1 Width | 11.0 cm |
| Package 1 Length | 20.0 cm |
| Package 1 Weight | 2.082 kg |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 1 |
| Package 2 Height | 14.0 cm |
| Package 2 Width | 11.0 cm |
| Package 2 Length | 20.0 cm |
| Package 2 Weight | 2.19 kg |
| Unit Type of Package 3 | S03 |
| Number of Units in Package 3 | 4 |
| Package 3 Height | 30.0 cm |
| Package 3 Width | 30.0 cm |
| Package 3 Length | 40.0 cm |
| Package 3 Weight | 8.328 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | <input checked="" type="checkbox"/> REACH Declaration |
| EU RoHS Directive | Compliant <input checked="" type="checkbox"/> EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | <input checked="" type="checkbox"/> Yes |
| China RoHS Regulation | <input checked="" type="checkbox"/> China RoHS Declaration |
| Environmental Disclosure | <input checked="" type="checkbox"/> Product Environmental Profile |
| Circularity Profile | <input checked="" type="checkbox"/> End Of Life Information |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|