




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Cluster Blocks



Number of Circuits: 2

Primary Product Material: PBT GF

Features

Product Type Features

Compatible With Discrete Wire Type	Magnet Wire
------------------------------------	-------------

Configuration Features

Number of Circuits	2
--------------------	---

Body Features

Primary Product Color	Natural
Primary Product Material	PBT GF

Contact Features

Mating Pin Diameter	2.29 mm[.09 in]
---------------------	-----------------

Mechanical Attachment

Block Mounting Configuration	2 Forward - 1 Back
------------------------------	--------------------

Dimensions

Compatible Insulation Diameter Range	1.5 – 2.6 mm[.059 – .103 in]
Product Length	30.5 mm[1.2 in]

Packaging Features

Packaging Method	Box
Packaging Quantity	5000



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



TE Part #281006-4
CLUSTER BLOCK .090 DIA.




TE Part #360052-1
125 DIA CLSTR BLK



TE Part #284633-1
SPEC. CLUSTER CONTACT TIN PLAT



TE Part #6-62131-3
CLSTR PIN RCPT



TE Part #62244-6
125 PIN RECEPTACLE 18-16

Documents

Product Drawings

CLUSTER BLOCK HSG .090 DIA. RE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_284406-1_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_284406-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_284406-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Magnet Wire Terminals & Splices

English

Product Specifications

Special rec. cluster ctc. f. 090 dia. p/n 284633-1

English

Application Specification

English



Agency Approvals

UL Report

English