



HT-SCE

TE Internal #: 131854-000
Ladder, High Temperature, 2:1, Black, 1 Markers per Sleeve, 50.8 mm [2 in] Length, 19 mm [.75 in] Expanded Inside, HT-SCE, Printable Tubing

[View on TE.com >](#)

Identification & Labeling > Printable Tubing > HT-SCE High Temperature Sleeves



Printable Tubing Type: **Ladder**
Printable Tubing Grade: **High Temperature**
Shrink Ratio: **2:1**
Primary Product Color: **Black**
Markers per Sleeve: **1**

[All HT-SCE High Temperature Sleeves \(51\)](#)

Features

Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	High Temperature

Body Features

Shrink Ratio	2:1
Primary Product Color	Black
Markers per Sleeve	1

Dimensions

Product Length	50.8 mm[2 in]
Expanded Inside Diameter (Min)	19 mm[.75 in]
Recovered Inside Diameter (Max)	9.53 mm[.375 in]
Compatible Cable Diameter Range	9.9 – 15.3 mm[.39 – .602 in]

Usage Conditions

Operating Temperature Range	-55 – 225 °C[-67 – 437 °F]
-----------------------------	----------------------------

Printer/Label Features

Printer Technology	Thermal Transfer
--------------------	------------------

Packaging Features

Packaging Quantity	1000
--------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186501-1
T3212-SWARE-PRINTER



TE Part # 1-2186500-1
T3212-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 1-2186503-1
T3224-SWARE-PRINTER



TE Part # 154739-000
T300-RIBBON-WH-4HT

Also in the Series | HT-SCE



Printable Tubing(16)

Customers Also Bought



TE Part #695052-000
W-096-03



TE Part #0641-1-20233
CONT PIN



TE Part #A165103001
RAY-101-7.5(100)



TE Part #5070104028
RNF-100-1-X-SP



TE Part #CB7839-000
RW-200-1/2-0-SP



TE Part #6641710001
TMS-SCE-1/4-2.0-9



TE Part #CAT-T3437-H85999A
HT-SCE High Temperature Sleeves



TE Part #695051-000
W-096-02

Documents

Datasheets & Catalog Pages

HT-SCE High Temperature Heat Shrink Identification System

English

Product Specifications

IDENTIFCATION PRINTER PRODUCT RIBBON MATRIX

English



Instruction Sheets

Instruction Sheet (non U.S.)

English