



BROWN  
CRAZY HORSE  
LEATHER

# #143

MEN'S SIZES

3-14

HALF SIZES

7.5-10.5

Note: sizes 3, 4 & 14 have rubber outsoles

WIDE FIT

WATER RESISTANT UPPER

LUXURY COMFORT ARCH FOOTBED



PRODUCT CERTIFICATION



BSI Certified Product

CERTIFIED TO:  
Standard AS 2210.3:2019  
ASTM F2413 - 18 including EH (Clause 5.6)

These water-resistant boots are a great option for all day comfort and are packed with safety features. With an upper built with top-of-the-range Crazy Horse leather, each pair has it's own, unique look.

- Crazy Horse premium water-resistant leather lace up ankle safety boot—150mm height
- Padded collar and tongue
- Breathable, moisture wicking lining
- Moulded TPU heel guard
- PU midsole and TPU outsole highly resistant to hydrolysis and microbial attack
  - 6mm tread—oil, acid & organic fat resistant
  - heat resistant to 140°C
  - slip resistant
- SPS Max—XRD® Technology in the heel and forepart strike zones for increased impact protection
- Removable Comfort Arch footbed with XRD® Extreme Impact Protection forepart insert provides superior comfort
- Anti-bacterial, washable and breathable footbed
- Electrical hazard resistant
- Reinforced stitching
- Steel shank—ensures correct step flex point, assists with torsional stability
- Broad fitting Type 1 steel toe cap tested to resist a 200 joule impact



Refer to [blundstone.com.au](http://blundstone.com.au) for further details of the 30 day comfort guarantee and the manufacturers warranty.

PU - Polyurethane | TPU - Thermoplastic Polyurethane  
EVA - Ethel Vinyl Acetate | PUR - Polyurethane Rubber  
XRD® is a registered trademark of Rogers Corporation.

SAFETY

#143

