

4, 5, and 6-Wire Receptacles, Front Mount, 1/2-14 NPSM Threads

- NEMA 1, 3, 4, 6P
- IEC IP68 Protection



Housing Style	Female Part Number	Male Part Number	Features	Pinout
<p><b>FK ..14.5</b></p> <p>Typical panel cutout is 21 mm.</p>	FK 4.4-*/14.5	FS 4.4-*/14.5	4x22 AWG, 105°C, 250 VAC/ 300 VDC, 4 A, mates with 4-pin cordsets	<p><b>Female</b></p> <p><b>Male</b></p>
	FK 4.4-*/14.5/S613	FS 4.4-*/14.5/S613	4x18 AWG, 105°C, 250 VAC/VDC, 4 A, mates with 4-pin cordsets	<p>1. BN 2. WH 3. BU 4. BK</p>
	FK 4.4-*/14.5/S621	FS 4.4-*/14.5/S621	4x18 AWG, 105°C, 250 VAC/300 VDC, 4 A, mates with 4-pin cordsets	<p>1. GY1 2. GY2 3. GY3 4. GY4</p>
<p><b>FS .. 14.5</b></p> <p>Typical panel cutout is 21 mm.</p>	FK 4.5-*/14.5	FS 4.5-*/14.5	5x22 AWG, 105°C, 250 V, 4 A, mates with 5-pin cordsets	<p><b>Female</b></p> <p><b>Male</b></p>
	FK 4.6-*/14.5	FS 4.6-*/14.5	6x22 AWG, 105°C, 250 V, 4 A, mates with 6-pin cordsets	<p>1. BN 2. WH 3. BU 4. BK 5. GY 6. PK</p>
	FK 6-*/14.5	FS 6-*/14.5	6x24 AWG, 105°C, 60 VAC/75 VDC, 2 A, mates with 6-pin cordsets	<p><b>Female</b></p> <p><b>Male</b></p>

\* Length in meters. Standard cable length is 0.5 Meters. Consult factory for other lengths.  
 Standard housing material is nickel plated brass "FS.."; "FSV.." indicates stainless steel.  
 To specify PVC jacketed cable, add "/S717" to the end of the part number.