Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



PILOT LIGHT 120VAC 30MM SK +OPTIONS

Local distributor code:

9001SKP1G9

EAN Code: 3389118037687

Main

Range of product	Harmony 9001SK	
Product or component type	Pilot light	
Device short name	9001SK	
Lens type	Domed plastic	
Light block supply	Via integral transformer 120 V AC 50/60 Hz 6 V)	

Complementary

Bezel material	Plastic	
Mounting diameter	30 mm	
Shape of signaling unit head	Round	
Cap/operator or lens colour	Green	
Light source	incandescent	
Bulb base	BA 9s	
[Us] rated supply voltage	110120 V AC 50/60 Hz	
Tightening torque	0.8 N.m conforming to EN/IEC 60947-1	
Shape of screw head	Cross slotted	
Connections - terminals	Screw clamp terminals, 1 x 0.222 x 1.5 mm² conforming to EN/IEC 60947-1	
[Ith] conventional free air thermal current	10 A	
Short-circuit protection	10 A cartridge fuse conforming to EN/IEC 60947-5-1	
[Ui] rated insulation voltage	250 V (pollution degree 2) conforming to EN/IEC 60947-1	
[Uimp] rated impulse withstand voltage	2.5 kV conforming to EN/IEC 60947-1	
Operating position	Any position	
CAD overall width	54 mm	
CAD overall height	70 mm	
CAD overall depth	42 mm	
Net weight	0.181 kg	
Device presentation	Complete product	
Lens type	Domed	
[Us] rated supply voltage	110120 V	
Light block supply	Via integral transformer	
Supply frequency	5060 Hz	

Lens material	Polycarbonate	
Size	30 mm	
Light source	Incandescent bulb	

Environment

Electrical shock protection class	Class II conforming to IEC 61140	
Protective treatment	TC	
IP degree of protection	IP66 conforming to IEC 60529	
NEMA degree of protection	NEMA 1	
	NEMA 12	
	NEMA 13	
	NEMA 2	
	NEMA 3	
	NEMA 3R	
	NEMA 4	
	NEMA 4X	
Vibration resistance	7 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock resistance	50 gn conforming to IEC 60068-2-27	
Ambient air temperature for operation	-2570 °C	
Ambient air temperature for storage	-4070 °C	
Standards	JIS C 852	
	CSA C22.2 No 14	
	EN/IEC 60947-5-1	
	EN/IEC 60947-1	
	JIS C8201-5-1	
	UL 508	
	EN/IEC 60947-5-4	
	JIS C8201-1	
Product certifications	UL 508	
	NEMA	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.572 cm
Package 1 Width	5.588 cm
Package 1 Length	9.398 cm
Package 1 Weight	163.293 g

Logistical informations

Country of origin FR

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes	
Packaging without single use plastic	Yes	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
REACh Regulation	REACh Declaration	


Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

9001SKP1G9

Dimensions Drawings

Dimensions



 \boldsymbol{e} panel thickness: 1 to 6 mm / 0.04 to 0.24 in.

Image of product / Alternate images

Alternative







