




Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Hardware



Hardware Type: **Grommet**

Connector System: **Wire-to-Wire**

Sealable: **No**

Operating Temperature Range: **-55 – 85 °C [-67 – 185 °F]**

Features

Product Type Features

Product Type	Accessory
Accessory Color	Black
Connector System	Wire-to-Wire
Sealable	No

Body Features

Color	Black
Material	Flexible PVC

Mechanical Attachment

Hardware Type	Grommet
---------------	---------

Dimensions

Height	9.53 mm[.375 in]
Length	10.67 mm[.42 in]

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

For Use With	Connector
--------------	-----------

Packaging Features

Packaging Quantity	500
Packaging Method	Bag



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

TE Part # 350522-1
09P STR/REL HSG HNGD V0


TE Part # 350523-1
15P STR/REL HSG HNGD V0

TE Part # 350374-1
12P STR/REL HSG HNGD V0

Customers Also Bought




TE Part #745229-2
20 DF PIN PLTD 30 SEL



TE Part #1-640523-0
15P MR II PLUG HSG V0



TE Part #2-34160-1
TERMINAL,PG R 16-14 8, TAPE




TE Part #350968-2
MR PIN 26-24 AU/PHBZ




TE Part #794230-1
MINI UMNL2 PIN 20-16AWG LP SN




TE Part #323096
SOLIS R 22-16 COMM 22-18 MIL 4



TE Part #1-5207908-0
KIT S/R SCREW RET 90/180 DEG



TE Part #350523-1
15P STR/REL HSG HNGD V0



TE Part #2-350376-0
MR SPLT GROMET .218 DIA BLK LF



TE Part #2-350377-0
MR SPLT GROMET .156 DIA BLK LF

Documents

Product Drawings

MR SPLT GROMET .218 DIA BLK LF

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-350378-1_U.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-350378-1_U.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-350378-1_U.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English