

4, 5 and 6-Wire *microfast*® Cordsets, Standard Duty

- Straight Female Connectors
- NEMA 1, 3, 4, 6P and IEC IP 67 Protection
- 250 V, 4.0 A



Housing Style	Part Number	Cable	Features	Pinout
	KB 4T-*	AWM PVC Yellow 4x22 AWG 105°C 5.2 mm OD Cable #RF50555-*M†	<i>flexlife</i> ®	
	KB 4T-*/S90	AWM PUR Yellow 4x22 AWG 105°C 5.7 mm OD Cable #RF50614-*M†	<i>Cut/Abrasion Immune</i>	1. RD/BK 2. RD/WH 3. RD 4. GN
	KB 4T-*/S105	AWM PVC Yellow 4x22 AWG 105°C 5.7 mm OD Cable #RF50656-*M†	<i>Braided Copper Shield</i>	
	KB 4T-*/S727	AWM PUR Grey 4x22 AWG 105°C 5.2 mm OD Cable #RF50532-*M†	<i>Special Conductor Color Code</i>	1. BN 2. BU 3. BK 4. WH
	KB 5T-*	AWM PVC Yellow 5x22 AWG 105°C 5.7mm OD Cable #RF50556-*M†	<i>flexlife</i>	1. RD/WH 2. RD 3. GN 4. RD/YE 5. RD/BK
	KB 6T-*	AWM PVC Yellow 6x22 AWG 105°C 6.2mm OD Cable #RF51003-*M†	<i>flexlife</i>	1. RD/WH 2. RD 3. GN 4. RD/YE 5. RD/BK 6. RD/BU

Cordsets

* Length in meters. Standard cable lengths are 2, 4, 6, 8 and 10 meters. Consult factory for other lengths.
 ** Standard coupling nut material is nickel plated brass "KB .."; "KBK .." indicates nylon and "KBV .." indicates 316 stainless steel.
 † See Section N for *reelfast*® cable information.