


Parker Product Datasheet



Quick coupling system with nominal diameter 2.7 for pneumatic, liquids and gas applications up to 35 bar. Available in nickel-plated brass or stainless steel.

PART NUMBER: 20KBKO04RVX
COUPLING HALF: Coupler
FUNCTION: Double Shut-Off
BODY MATERIAL: Stainless Steel 303
CONNECTION TYPE: Tube
CONNECTION SIZE: 3x4 MM

PRODUCT OVERVIEW

Parker's Series 20 is a mini-industrial coupling with European profile. Coupling system with single-hand operation. High flow rate despite small dimensions.

Markets:

- Industrial
- Life Sciences
- Medical technology
- Chemistry pharmacybr/>>- Electronics and energy management
- Transportation
- Machinery construction
- Automotive
- Process

Features/Benefits:

- Mini Industrial coupling
- Single hand operation for easy and fast connection
- European profile is the most representative profile worldwide

TECH SPECIFICATIONS

DIVISION	Low Pressure Connectors Europe Division
FOR FLUID TYPE	Chemicals (Paints, solvents, lubricants)
DIAMETER	2.7 mm (nominal)
PRODUCT SERIES	Series 20
FLOW RATE	1.2 L/min (water)
FOR FLUID TYPE	Water (Industrial, drinking, treated water)
INDUSTRY	Electronics
COMPATIBLE FITTING	Series 20 Plug
APPLICATION	Pharma
CONNECTION TYPE	Tube With hose nut, without spring guard
REGION OF ORIGIN	Germany
INDUSTRY	Healthcare & Life Sciences
MAXIMUM OPERATING PRESSURE	35 bar
HEX SIZE	9 mm (external)
FUNCTION	Double Shut-Off
OPERATION TYPE	Sleeve
INTERCHANGE TYPE	European Profile
APPLICATION	Medical
VALVE INCLUDED	Yes
PRODUCT STYLE	Quick Connect
CONNECTION SIZE	3x4 mm
LENGTH	34 mm

APPLICATION	Electronics
SLEEVE MATERIAL	Stainless Steel 303
SEAL MATERIAL	FKM
TECHNOLOGY	Pneumatics
BRAND	Rectus
MAXIMUM OPERATING TEMPERATURE	392 °F
APPLICATION	Food & Beverages
PLATING TYPE	Without Surface Treatment
COUPLING HALF	Coupler
BRAND	Parker
MINIMUM OPERATING TEMPERATURE	-15 °C
APPLICATION	Industrial Machinery
DIVISION	Low Pressure Connectors Europe Division
QUANTITY PER BOX	2.0
MAXIMUM OPERATING TEMPERATURE	200 °C
MINIMUM OPERATING TEMPERATURE	5 °F
APPLICATION	Energy Management
VALVE TYPE	Standard Valve
FLOW RATE	130 L/min (air)
BODY MATERIAL	Stainless Steel 303
TECHNOLOGY	Fluid & Gas Handling
PRODUCT TYPE	Pneumatic Quick Couplings
MAXIMUM OPERATING PRESSURE	507 psi
INDUSTRY	General Industrial

FOR FLUID TYPE

Air & Neutral Gases (Industrial compressed, lubricated
air, inert gases)

WEIGHT

0.011 kg