



EN ISO 20345:2011



TOURING DEALER BOOT 10349-01L

S3 *CI SRC
Size: 36-48
Weight: 620 gr.

Fit: 11

Working Environment:
 Multipurpose, Logistics and Light Industry, Farming and Gardening, Building


FEATURES

UPPER

Greased Nubuk Dakar Leather Hydro 1,8-2,0 mm

LINING

Soft Full Grain Leather Hydro 3D Air circulation 320 gr.

ANTISLIP LINING

DUALMICRO

INSOLE

Climaction-Fit 337

TOE CAP

Fiber cap SXT

RESISTANCE TO PERFORATION

KX Antiperforation PS

TYPE

Ankle boot

SOLE

PU DUAL-DENSITY SRC

Two-component PU sole. Outsole suitable for indoor and outdoor use. Light and comfortable. Very flexible. Self-cleaning design and highly anti-slip. SRC Antislip Standard.

TECHNOLOGIES

Removable Insole

337 climaction fit

Removable anatomic and ergonomic insole. Absorbent and transpiring open-cell foam support. Keeps feet fresh. Specifically-designed thermoforming for exceptional comfort.



Protection elements


 RESISTANT
TO 3.0 mm.
NAILS

 fiber cap **sxt**

Composite toecap with fiberglass. Resistant to over 200J. Non metal perforation resistant insert to over 1100 N with a 3.0 mm truncated cone nail. Protection over the entire sole of the foot. Flexible and comfortable



Lateral stability

dynamic HC control technology

Ergonomic rigid internal structure. It houses the heel into the right seat, adjusting the foot support and control of the ankle sideways movements. It keeps the foot tight to the shoe, allowing the perfect fit.



Torsional stability

STABIL•ACTIVE

Support made of rigid plastic material. It stabilizes the heel bone, the instep and tarsal joints, without altering energy absorption. A support for the natural movement of the foot; it provides comfort and greater stability.




Electrical features



Wire Electricity Discharge

Strip with 4 filaments of carbon fiber, ensuring proven anti-static properties of the footwear over time.



Other

DUALMICRO DUALWICKO

Double non-slip layer of microfibre, resistant up to 200,000 cycles. Makes the footwear more comfortable, blocking the foot during use.



SRC (SRA+SRB)


 SOLE TO
PU - PU

SRA CERAMIC + DETERGENT SOLUTION	FLAT ≥0.32 HEEL (CONTACT ANGLE °°) ≥0.28	0.39
SRB STEEL + GLYCEROL	FLAT ≥0.18 HEEL (CONTACT ANGLE °°) ≥0.13	0.19
		0.14

EN ISO 20344:2011