

Technical data



21320D1C3

Spherical roller bearings



Spherical roller bearing, one-piece machined cage, groove and lubrication holes on outer ring

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	100 mm
D - External diameter	215 mm
B - Bearing/Inner ring width	47 mm
d2 - External diameter inner ring	137 mm
D1 - Inner diameter outer ring	178,7 mm
rs - Min fillet radius	3 mm
Number of lubrication holes	4
b - Groove width	9 mm
k - Hole diameter	5 mm
Radial clearance class	C3
Mass	8,89 kg

PRODUCT PERFORMANCE

C - Dynamic load	410000000 mN
C0 - Static load	465000000 mN
Cu - Fatigue limit load	42500000 mN
e - Coefficient	0.22
Y0 - Static axial load coefficient	2.94
Y1 - Lower axial load coefficient	3.01
Y2 - Upper axial load coefficient	4.48
N lim - Oil lubrication limit speed	15600 °/s
N lim - Grease lubrication limit speed	12000 °/s
Tmin - Min operating temperature	233,15 °K



PRODUCT PERFORMANCE

Tmax - Max operating temperature	393,15 °K
---	-----------

ABUTMENT

da min - Min shoulder diameter IR	114 mm
Da max - Max shoulder diameter OR	201 mm
ra max - Max shaft & housing fillet radius	2,5 mm

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = X.F_r + Y.F_a$$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	Y1	0.67	Y2

Equivalent static radial load

$$P_0 = X_0.F_r + Y_0.F_a$$

X_0	Y_0
1	Y0

The values for e, Y1, Y2 and Y0 are shown in the above table .



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15