



Part Number: 5200FE

Security & Sound, 2 Conductor 16 AWG, BC, CMR

Product Description

Security & Commercial Audio Cable, Riser-CMR, 2-16 AWG stranded bare copper conductors with polyolefin insulation, Beldfoil® shield and PVC jacket with ripcord

Technical Specifications

Product Overview

Environmental Space:	Indoor - Riser
Suitable Applications:	Intercom/PA Systems, Sound/Audio Systems

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
16	19x29	BC - Bare Copper	2

Conductor Count:	2
Conductor Size:	16 AWG

Insulation

Material	Nominal Wall Thickness
PP - Polypropylene	0.008 in

Color Chart

Number	Color
1	Black
2	Red

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	24	Solid

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.188 in	0.017 in	Yes

Construction and Dimensions

Cabling

Lay Direction	Twists
Left Hand	4 twist/ft

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
4 Ohm/1000ft	14.4 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
58 pF/ft	114 pF/ft

Inductance

Nominal Inductance
0.14 µH/ft

Current

Element	Max. Recommended Current [A]
10C Temperature Rise	Per conductor @ 25°C ambient: 6.25 A

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	26 lbs/1000ft
Max Recommended Pulling Tension:	85.5 lbs
Min Bend Radius/Minor Axis:	2.0 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMG
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1666 Vertical Shaft
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	N
Plenum Number:	6200FH

Part Number

Variants

Item #	Color	Footnote
5200FE 0101000	Black	

5200FE 010Z1000	Black	
5200FE 010Z1000	Black	
5200FE 0061000	Blue, Light	
5200FE.00152	Chrome	
5200FE.00305	Chrome	
5200FE.00153	Chrome	
5200FE.001500	Gray	
5200FE.00U305	Gray	
5200FE 0081000	Gray	C
5200FE 008500	Gray	C
5200FE 008U1000	Gray	
5200FE 008U500	Gray	
5200FE.001525	Gray	
5200FE 008Z1000	Gray	
5200FE 008Z1000	Gray	
5200FE 0051000	Green, Dark	
5200FE 0031000	Orange	
5200FE 0021000	Red	
5200FE 002Z1000	Red	
5200FE 002Z1000	Red	
5200FE 0071000	Violet	
5200FE 009U1000	White	
5200FE 0091000	White	
5200FE 009Z1000	White	
5200FE 009Z1000	White	
5200FE 0041000	Yellow	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.