



Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**
Packaging Method: **Bag**
Tensile Strength: **133.44 Newton**
Product Length: **148 mm [5.83 in]**

Features

Product Type Features

Cable Tie Style	Standard
Tensile Strength	133.44 Newton

Body Features

Primary Product Color	Black
Primary Product Material	Nylon

Dimensions

Compatible Cable Bundle Diameter Range	31.75 mm[1.25 in]
Product Length	148 mm[5.83 in]
Product Width	3.6 mm[.142 in]
Product Thickness	1.1 mm[.043 in]

Packaging Features

Packaging Method	Bag
Packaging Quantity	100

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)
Candidate List Declared Against: JAN 2025 (247)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 4-1579002-9
CABLE TIE TOOL


Customers Also Bought




TE Part #2325080-5
LIGHTPIPE ASSEMBLY, OSFP



TE Part #2041313-4
PCI-E, Straddle, 164P, 30u", P



TE Part #1-1932031-2
VERTICAL DDR3 DIMM, 240 POSITION, LR



TE Part #5-2213818-1
6X6 ILL TACT THT 520GF YELLOW GREEN





TE Part #1-1986469-2

TSB2000K12DSHT=EUROPA BL,14.5M




TE Part #6-103916-4

60 sys 50 hdr drst unshrd sn



TE Part #2315853-4

CAGE ASSEMBLY, 1X4, NO EMI SPRINGS, OSFP




TE Part #1274531-1

N SERIES, SURFACE MOUNT PCB



TE Part #YDTS24W17-35JNV001

RECP ASSY



TE Part #1-647000-2

12P MTA100 PSTD CONN ASSY SN

Documents

Product Drawings

CABLE TIE, BLACK, 6" L, 100/PACK

English

Datasheets & Catalog Pages

CABLE TIES

English