




Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Dust Cap**
Primary Product Color: **Black**
Primary Product Material: **Elastomer**
Operating Temperature (Max): **105 °C [221 °F]**
Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Connector Cover Type	Dust Cap
----------------------	----------

Body Features

Primary Product Color	Black
Primary Product Material	Elastomer

Mechanical Attachment

Component Retention Feature	Push/Pull
-----------------------------	-----------

Housing Features

Compatible With Connector Shape	Circular
---------------------------------	----------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Compatible With Connector Shell Size	11
--------------------------------------	----

Packaging Features

Packaging Method	Bag
Packaging Quantity	1000

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1445818-1
PLUG,11-7,SM INS,STD KEY



TE Part # 1445819-1
PLUG,11-6,SM INS,STD KEY



TE Part # 1445821-1
REC,11-8,FLNG MT,SM INS,STD KE



TE Part # 1445824-1
REC,11-5,FLNG MT,SM INS,STD KE



TE Part # 1445827-3
REC,11-7,FRE HNG,LG INS,STD KE



TE Part # 1445817-1
PLUG,11-8,SM INS,STD KEY



TE Part # 1445819-3
PLUG,11-6,LG INS,STD KEY



TE Part # 1445829-1
REC,11-5,FRE HNG,SM INS,STD KE





TE Part # 1445821-3
REC,11-8,FLNG MT,LG INS,STD KE



TE Part # 1445822-1
REC,11-7,FLNG MT,SM INS,STD KE



TE Part # 1445825-1
RECPT,11-9,FREE HNG,STD KEY



TE Part # 1445820-1
PLUG,11-5,SM INS,STD KEY



TE Part # 1445822-3
REC,11-7,FLNG MT,LG INS,STD KE



TE Part # 1445807-1
PLUG,11-9,SM INS,STD KEY



TE Part # 1445807-3
PLUG,11-9,LG INS,STD KEY



TE Part # 1445829-3
REC,11-5,FRE HNG,LG INS,STD KE



TE Part # 1445820-3
PLUG,11-5,LG INS,STD KEY



TE Part # 1445825-3
RECPT,11-9,FREE HNG,STD KEY



TE Part # 1445828-3
REC,11-6,FRE HNG,LG INS,STD KE



TE Part # 1445818-3
PLUG,11-7,LG INS,STD KEY

Also in the Series | AMP Circular Plastic Connectors



Circular Power Connectors(423)



Connector Backshells(1)



Connector Caps & Covers(16)



Connector Seals & Cavity Plugs(35)




Connector Strain Relief(60)




Insertion & Extraction Tools(1)

Customers Also Bought






TE Part #1445856-1
STR RELIEF ASY, STRAIGHT SZ 11




TE Part #2-2213767-3
AV19 SPL 3A MOVE RING LED WHITE 24V




TE Part #332985-000
TMS-SCE-1K-3/8-2.0-0




TE Part #1977876-1
SLD CPC RCPT ASY, 11-4, STD SEX, UV RESIST



TE Part #81665-3
ECONOSEAL, FLANGE GASKET



TE Part #1445816-3
RECPT, 11-9, FLNG MT, STD KEY



TE Part #97H1-23-1-B
97H1-23-1-B



TE Part #4584443001
44A0111-14-9CK0001



TE Part #ER6595-000
D-436-38CS9376



TE Part #1445534-3
PLUG, 8-3, LARGE INS, STD KEY

Documents

Product Drawings
CAP,DUST,SIZE 11

English

CAD Files

Customer View Model
ENG_CVM_1604089-2_A.3d_igs.zip

English

Customer View Model
ENG_CVM_1604089-2_A.3d_stp.zip

English

Customer View Model
ENG_CVM_1604089-2_A.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[1-1773902-9_CPC_Catalog](#)

English

[1-1773902-9_CPC_Catalog](#)

[1-1773902-9_CPC_Catalog](#)

German

[1-1773902-9_CPC_Catalog](#)

Japanese

[AMP Circular Connectors for Commercial Signal & Power Applications Continued](#)

English

[Product Specifications](#)

[Application Specification](#)

English