

NOTES:

1. MATERIALS

1.1 CABLE: (7/0.12BC*1P+7/0.12BC+FAM)*2+7/0.20TC*2C+
7/0.12TC*1P+AL+7/0.12BC+128/0.12ALM+WHITE PVC JACKET.
OD=5.5 ± 0.2MM.

CABLE MARKING: E324703 AWM STYLE 2725 80°C 30V USB 3.0 CABLE

1.2 P1: USB3.0 A TYPE MALE: SOLDER TYPE, GOLD PLATED CONTACTS, NICKEL PLATED SHELL.
P2: USB3.0 B TYPE MALE: SOLDER TYPE, GOLD PLATED CONTACTS, NICKEL PLATED SHELL.

1.3 ALL HOOD: MOLDED WHITE PVC.

2. ELECTRICAL

2.1 100% OPEN AND SHORT TEST.
2.2 CONDUCTOR RESISTANCE: 5 OHMS MAX.
2.3 INSULATION RESISTANCE: 5 MEGOHMS MIN.
2.4 HI-POT: DC300V/0.01S.


3. PACKING: SPECIFIC SEE PACKAGING FIGURE.

3. ALL MATERIAL BE ROHS AND REACH COMPLIANT.

PIN UOT

AM		BM
1	—————	1
2	—————	2
3	—————	3
4	—————	4
5	—————	5
6	—————	6
7	—————	7
8	—————	8
9	—————	9

SHELL BRAID+DRAIN SHELL



LENGTH TOLERANCE: X. ± 0.5 .X ± 0.2 .XX ± 0.1	SCALE: FREE	
ANGLE TOLERANCE: X° ± 3° .X° ± 1°	UNIT: mm	
	VERSION: 00	PAGE: 1/1

VALUE USB 3.0 Cable, Type A M-B M

DRAWING NO:
0276

Item No.: 11.99.8869

00	NEW ISSUE	2011-8-31
REV.	MODIFY DESCRIPTION	DATE