


RS PRO Miniature Micro Switch

RS Stock No.: 241-240

Features

- VERSATILE SWITCH SUITABLE FOR HEAVY DUTY APPLICATIONS.
- COMPATIBLE WITH ALL INDUSTRY STANDARD V3 SWITCHES.
- AVAILABLE WITH SOLDER, QUICK CONNECT AND SCREW TERMINALS
- LONG MECHANICAL AND ELECTRICAL LIFE.
- FINE SILVER CONTACTS
- TEMPERATURE RANGE UPTO 85°C
- POSITIVE SNAP ACTION
- CONFORM TO IEC 1508-1 STANDARD.

CE /  / 
APPROVED.



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Versatile switch suitable for many heavy duty applications
- Compatible with all industry standard V3 switches.
- Available with solder, quick connect and screw terminals.
- Fine silver contacts.
- Long mechanical and electrical life.
- Temperature range upto 85 °c
- Positive snap action.
- Confirm to IEC 1058-1-standard

General Specifications

Contact Configuration	SPDT.
Contact Arrangement	1No + 1NC,snap action.
Contacts	Pure silver, bi-metal, silver plated.
Terminals	Copper alloy, silver plated.
Plunger	Nylon.
Case	30% Glass filled flame retardant thermoplastic UL94 V0.
Salient Feature	Stainless steel long Plain lever (27.5 mm) and 4.75X0.5mm quick-connect terminals.

Electrical Specifications

Electrical Rating		
	Load	Rating
	AC-15	16 Amp at 250V.
		5 Amp at 440V.
	DC-13	0.6 Amp at 110V (Resistive).
		0.3 Amp at 220V (Resistive).
		0.1 Amp at 110V (Inductive).
		0.05 Amp at 220V (Inductive).
Contact Resistance		15 milliohms max. (initial).
Insulation Resistance		100 Megaohms (min.) at 500V DC.
Voltage Proof		1500V AC between each shorted terminal with body and 1000V AC between open contacts.
Electrical life		50,000 operations at 16A, 250V AC.
Mechanical life		100000 operations.

Mechanical Specifications

Operating Force (OF)	125gms. (max).
Release Force(RF)	14gms.(min.).
Pretravel (PT)	4.0 mm. (max.).
Movement Differential (MD)	1.5 mm. (max.).
Overtravel (OT)	1.6 mm.
Operating Position (OP)	15.2±1.2mm.
Mounting	Side mounted, use two M3 screws with plain washers or spring washers. Tighten the screws at a torque of 3 kg-cm.
Unit Weight	7.4gms. Approx.

Operation Environment Specifications

Operating Temperature Range	-55°C to +85°C.
-----------------------------	-----------------

Protection Category

IP Rating	IP40(enclosure).
-----------	------------------

Approvals

Compliance/Certifications	  CE/ C us / CA
---------------------------	---

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories