




Connectors > PCB Connectors > Backplane Connectors > Hard Metric Backplane Connectors



PCB Connector Type: **PCB Mount Receptacle**
Data Rate: **1 Gb/s**
Number of Columns: **22**
Number of Rows: **5**
Backplane Architecture: **Traditional Backplane**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
PCB Connector Type	PCB Mount Receptacle
Sealable	No

Configuration Features

Number of Columns	22
Number of Rows	5
Backplane Architecture	Traditional Backplane
Number of Positions	110
PCB Mount Orientation	Right Angle

Signal Characteristics

Data Rate	1 Gb/s
-----------	--------

Body Features

Primary Product Color	Gray
-----------------------	------



Contact Features

Contact Underplating Material	Nickel
Contact Base Material	Phosphor Bronze
CompactPCI Designation	None
Contact Mating Area Plating Material	Gold (Au)
Contact Mating Area Plating Material Thickness	.76 µm[29.92 µin]
Contact Current Rating (Max)	1.5 A

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Housing Material	Glass-Filled Polyester
Centerline (Pitch)	2 mm[.079 in]

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	11
Packaging Method	Tube

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900



ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 5338108-2
Z-PACK SHLD.LOWER A

TE Part # 5100143-1
2MM H.M. TYPE "A" PIN ASSY.

TE Part # 5-520424-3
8 SDL RND PLUG ASSY 50 SERIES

Also in the Series | Z-PACK 2mm HM

Backplane Connector Housings(4)

Backplane Power Connectors(1)

Connector Caps & Covers(62)

Hard Metric Backplane Connectors
(266)

Insertion & Extraction Tools(2)


PCB Headers & Receptacles(46)

Rectangular Power Connectors(46)

Customers Also Bought



TE Part #4-644759-2
12P MTA156 HDR ASSY STR LF




TE Part #862547-6
LEAD, SGL END ASSY, LGH



TE Part #2178531-4
Crown Clip Junior AG Plating Reflow




TE Part #2204167-1
MBXLE R/A RCPT,A/C PASS THRU
4ACP+12S+3P



TE Part #5106015-1
Z-PACK/A RAMH.110P




TE Part #172211-4
EIS CAP HSG FREE HANG 4P
NATUTURAL




TE Part #5352068-9
Z-PACK/A RAF 110P



TE Part #2143154-2
IMP100S,H,V5P14C,LG,REW39,4.9



TE Part #3-2323270-1
zSFP+ STACKED BELLY TO BELLY,
2X8 RECPT



TE Part #2402216-1
ZSFP+ 1X4 CAGE ASSEMBLY,
PRESSFIT, 1-LP

Documents

Product Drawings
Z-PACK/A F-HDR.110P EON

English

CAD Files
Customer View Model
ENG_CVM_CVM_1857989-1_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model
ENG_CVM_CVM_1857989-1_A.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_1857989-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English