




TE Internal #: 1827684-2

Board-to-Board, 7 Position, 2 mm [.079 in] Centerline, Receptacle, 30 VDC, Right Angle, Printed Circuit Board, Power & Signal, DC Jack Connectors

[View on TE.com >](#)

Connectors > PCB Connectors > Battery Connectors & Holders > DC Jack Connectors



Connector System: **Board-to-Board**

Number of Positions: **7**

Centerline (Pitch): **2 mm [.079 in]**

Connector & Housing Type: **Receptacle**

Operating Voltage: **30 VDC**

Features

Product Type Features

Connector System	Board-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	7
PCB Mount Orientation	Right Angle

Electrical Characteristics

Operating Voltage	30 VDC
-------------------	--------

Contact Features

Contact Current Rating (Max)	6 A
------------------------------	-----

Mechanical Attachment

PCB Mount Retention	Without
Connector Mounting Type	Board Mount

Housing Features



Centerline (Pitch)	2 mm[.079 in]
--------------------	---------------

Usage Conditions

Operating Temperature Range	-20 – 80 °C[-4 – 176 °F]
-----------------------------	--------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1827654-1
2mm pitch Battery Plug Assy. 7Pos.
H=4.0

Customers Also Bought



TE Part #1-1801178-6
3W RECEPTACLE HP CONNECTOR
BROWN



TE Part #2381809-1
2.5MM PITCH BATTERY REC. ASSY
8POS. R/A



TE Part #3-1418437-1
6POS,AMP MCP2.8,REC HSG,ASSY,
SEALED



TE Part #5646954-3
UPM 4 POSITION HEADER



TE Part #5-458141-7
CRIMPER, WIRE



TE Part #104130-2
014 LOPRO HDR RA 30DP LATCH



TE Part #HDP24-24-9PN-L015
REC, 9P, BLK, N, THD, 4/8/12, P



TE Part #HD36-18-14SN-L006
PLG,14P,AL,N,CBL CLMP BT,
NODRAIN,16,S,MC



TE Part #927884-2
CI 2 STIFT



TE Part #172315-7
PULSE LOCK PLUG HSG 10P YELLOW

Documents

Product Drawings

2mm pitch Battery Rec. Assy. 7Pos. H=4.0

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1827684-2_D.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1827684-2_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1827684-2_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1](#)

English

Product Specifications

[Product Specification](#)

English